







FRONT VIEW



SIDE VIEW




BOTTOM VIEW



RECOMMENDED PANEL CUTOUT

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	NEW PROPOSAL	JUL19/22	KELVIN



RECOMMENDED P.C.B LAYOUT
(TOLERANCE: $\pm 0.05[\pm .002]$)
(PCB TOLERANCE: $1.57[.062]$)
(COMPONENT SIDE OF PC BOARD)

NOTES:

1. MATERIALS:

CONTACTS: PHOSPHOR BRONZE, 0.35MM THICKNESS,
PLATING: 50μ "[1.27 MICRONS] MIN. GOLD PLATING
ON MATING SURFACES
 50μ "[1.27 MICRONS] MIN. NICKEL OVERALL.
GOLD FLASH ON CONTACT TAILS.

HOUSING: ENGINEERING THERMOPLASTIC, FLAMMABILITY RATING UL 94V-0
COLOR - BLACK.

2. MECHANICAL:

MATING FORCE: 5.0 LBS MAXIMUM

3. ELECTRICAL:

CONTACT RESISTANCE: 20 MILLIOHMS MAXIMUM
INSULATION RESISTANCE: 500 MEGOHMS MINIMUM
CURRENT RATING: 1.5 AMPS
VOLTAGE RATING: 125 VOLTS AC

4. ENVIRONMENTAL:

STORAGE TEMPERATURE: -40°C TO $+85^{\circ}\text{C}$

5. RECOMMENDED SOLDERING TEMPERATURE:

WAVE SOLDERING PEAKED AT 260°C FOR 5 TO 8 SECONDS.

AMPHENOL PART NUMBER: RJE7E-266-0400

UNLESS SPECIFIED OTHERWISE		DRAWN RONNIE.C		JUL19/22		Amphenol Canada Corp.					
PRIMARY UNITS MILLIMETERS		CHECKED KELVIN.T		JUL19/22		Commercial Products					
SECONDARY INCHES		M.E. APP'D				TWO PORT MODULAR JACK, TAB UP, 6 POSITION, 6 CONTACTS, UNSHIELD -RoHS COMPLIANT					
REFERENCE IN PARENTHESES		Q.A. APP'D									
GENERAL TOLERANCES		DWG APP'D									
1 DECIMAL PLACE ±0.35				ENG. REL. NO.							
2 DECIMAL PLACES ±0.25		REF.				DWG NO.		P-RJE7E-266-0400			REV A
3 DECIMAL PLACES ±0.13		THIRD ANGLE PROJECTION				DO NOT SCALE DRAWING					
ANGULAR DEGREES ±2.0°						CODE ID NO. 03554		DWG SIZE X	SCALE N/A	SHEET 1	OF 1