



Product: [7805R](#)

RF 100 Wireless Coax, RG174, 24.5 AWG, Foil + TC Braid, CMR/CMG PVC Jacket

Product Description

RF 100 Wireless Coax, RG-174 type, 24.5 AWG solid .020" bare copper conductor, foam HDPE insulation, Beldfoil®; tinned copper braid shield (90% coverage), CMR/CMG PVC jacket.

Technical Specifications

Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
30 MHz	216 W	216 W
50 MHz	154 W	154 W
150 MHz	74 W	74 W
220 MHz	57 W	57 W
450 MHz	34 W	34 W
900 MHz	21 W	21 W
1,500 MHz	14 W	14 W
2,000 MHz	12 W	13 W
2,500 MHz	10 W	12 W
3,500 MHz	8 W	10 W
4,500 MHz	7 W	9 W
6,000 MHz	5 W	8 W
4,500 MHz		7 W
5,800 MHz		5 W
6,000 MHz		5 W

Voltage

UL Voltage Rating
300 V RMS

VSWR

Frequency [MHz]
5 - 6000 MHz

Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	9 lbs/1000ft
Max. Pull Tension:	20 lbs
Min Bend Radius/Minor Axis:	1.25 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
RG Type:	174/U Type

Series Type:	RF 100
--------------	--------

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
7805R 008100	Gray	Reel	100 ft	612825189558
7805R 008500	Gray	Reel	500 ft	612825189572
7805R 0081000	Gray	Reel	1,000 ft	612825189565

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.
-----------	--

History

Update and Revision:	Revision Number: 0.274 Revision Date: 04-28-2020
----------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
24.5	Solid	BC - Bare Copper	0.0195 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.06 in

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Alum / Poly	Beldfoil®	100%
Braid	2	Tinned Copper (TC)		90%

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.11 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
27.3 Ohm/1000ft	9.3 Ohm/1000ft	9.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
26.2 pF/ft

Inductance

Nominal Inductance
0.068 µH/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	1.4 dB/100ft
10 MHz	2 dB/100ft
30 MHz	3.5 dB/100ft
50 MHz	4.6 dB/100ft
150 MHz	8 dB/100ft
220 MHz	9.6 dB/100ft
450 MHz	14 dB/100ft
900 MHz	20.2 dB/100ft
1500 MHz	26.6 dB/100ft
1800 MHz	29.5 dB/100ft
2000 MHz	31.2 dB/100ft
2500 MHz	35.4 dB/100ft
3000 MHz	39.4 dB/100ft
3500 MHz	43 dB/100ft
4500 MHz	50 dB/100ft
5800 MHz	59 dB/100ft
6000 MHz	60.6 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.38 ns/ft	73.5%

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
30 MHz	3.7 dB/100ft
50 MHz	4.7 dB/100ft
150 MHz	8.1 dB/100ft
220 MHz	9.83 dB/100ft
450 MHz	14.38 dB/100ft
900 MHz	20.97 dB/100ft
1500 MHz	27.99 dB/100ft
1800 MHz	30.78 dB/100ft
2000 MHz	32.87 dB/100ft
2500 MHz	37.38 dB/100ft
3000 MHz	42.49 dB/100ft
3500 MHz	46.9 dB/100ft
4500 MHz	53.72 dB/100ft
5800 MHz	65.1 dB/100ft
6000 MHz	66.5 dB/100ft

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

