

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

---

The logo for Renesas, featuring the word "RENESAS" in a bold, sans-serif font. The letter "R" is stylized with a square cutout at its top-left corner.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

## 400 mW DHD ZENER DIODE

### (DO-34)


#### DESCRIPTION

NEC Type RD2.0ES to RD39ES Series are planar type diodes into DO-34 Package (Body length 2.4 mm MAX.) with DHD (Double Heatsink Diode) construction having allowable power dissipation of 400 mW.

#### FEATURES

- DO-34 Glass sealed package

This diode can be inserted into a PC board with a shorter pitch (5 mm)



- Planar process
- DHD (Double Heatsink Diode) construction
- Vz Applied E24 standard

#### ORDERING INFORMATION


RD2.0ES to RD39ES with suffix "AB1", "AB2", or "AB3" should be applied for orders for suffix "AB".

#### APPLICATIONS

Circuits for Constant Voltage, Constant Current, Waveform clipper, Surge absorber, etc.

#### ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub> = 25°C)

Forward Current	I <sub>F</sub>	150 mA	
Power Dissipation	P	400 mW	to see Fig. 6
Surge Reverse Power	P <sub>RSM</sub>	100 W (t = 10 μs)	to see Fig. 10
Junction Temperature	T <sub>j</sub>	175°C	
Storage Temperature	T <sub>stg</sub>	-65 to +175°C	



The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.

Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.

**ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C)**

Type Number	Suffix	Zener Voltage V <sub>Z</sub> (V) <sup>Note 1</sup>			Dynamic Impedance Z <sub>Z</sub> (Ω) <sup>Note 2</sup>		Knee Dynamic Impedance Z <sub>ZK</sub> (Ω) <sup>Note 2</sup>		Reverse Current I <sub>R</sub> (μA)	
		MIN.	MAX.	I <sub>Z</sub> (mA)	MAX.	I <sub>Z</sub> (mA)	MAX.	I <sub>Z</sub> (mA)	MAX.	V <sub>R</sub> (V)
RD2.0ES	AB	1.88	2.20	5	100	5	1000	0.5	120	0.5
	AB1	1.88	2.10							
	AB2	2.02	2.20							
RD2.2ES	AB	2.12	2.41	5	100	5	1000	0.5	120	0.7
	AB1	2.12	2.30							
	AB2	2.22	2.41							
RD2.4ES	AB	2.33	2.63	5	100	5	1000	0.5	120	1.0
	AB1	2.33	2.52							
	AB2	2.43	2.63							
RD2.7ES	AB	2.54	2.91	5	110	5	1000	0.5	100	1.0
	AB1	2.54	2.75							
	AB2	2.69	2.91							
RD3.0ES	AB	2.85	3.22	5	120	5	1000	0.5	50	1.0
	AB1	2.85	3.07							
	AB2	3.01	3.22							
RD3.3ES	AB	3.16	3.53	5	120	5	1000	0.5	20	1.0
	AB1	3.16	3.38							
	AB2	3.32	3.53							
RD3.6ES	AB	3.47	3.83	5	120	5	1100	0.5	10	1.0
	AB1	3.47	3.68							
	AB2	3.62	3.83							
RD3.9ES	AB	3.77	4.14	5	120	5	1200	0.5	5	1.0
	AB1	3.77	3.98							
	AB2	3.92	4.14							
RD4.3ES	AB	4.05	4.53	5	120	5	1200	0.5	5	1.0
	AB1	4.05	4.26							
	AB2	4.20	4.40							
	AB3	4.34	4.53							
RD4.7ES	AB	4.47	4.91	5	100	5	1200	0.5	5	1.0
	AB1	4.47	4.65							
	AB2	4.59	4.77							
	AB3	4.71	4.91							
RD5.1ES	AB	4.85	5.35	5	70	5	1200	0.5	5	1.5
	AB1	4.85	5.03							
	AB2	4.97	5.18							
	AB3	5.12	5.35							
RD5.6ES	AB	5.29	5.88	5	40	5	900	0.5	5	2.5
	AB1	5.29	5.52							
	AB2	5.46	5.70							
	AB3	5.64	5.88							
RD6.2ES	AB	5.81	6.40	5	30	5	500	0.5	5	3.0
	AB1	5.81	6.06							
	AB2	5.99	6.24							
	AB3	6.16	6.40							
RD6.8ES	AB	6.32	6.97	5	25	5	150	0.5	2	3.5
	AB1	6.32	6.59							
	AB2	6.52	6.79							
	AB3	6.70	6.97							
RD7.5ES	AB	6.88	7.64	5	25	5	120	0.5	0.5	4.0
	AB1	6.88	7.19							
	AB2	7.11	7.41							
	AB3	7.33	7.64							
RD8.2ES	AB	7.56	8.41	5	20	5	120	0.5	0.5	5.0
	AB1	7.56	7.90							
	AB2	7.82	8.15							
	AB3	8.07	8.41							
RD9.1ES	AB	8.33	9.29	5	20	5	120	0.5	0.5	6.0
	AB1	8.33	8.70							
	AB2	8.61	8.99							
	AB3	8.89	9.29							
RD10ES	AB	9.19	10.30	5	20	5	120	0.5	0.2	7.0
	AB1	9.19	9.59							
	AB2	9.48	9.90							
	AB3	9.82	10.30							

Type Number	Suffix	Zener Voltage V <sub>Z</sub> (V) <sup>Note 1</sup>			Dynamic Impedance Z <sub>Z</sub> (Ω) <sup>Note 2</sup>		Knee Dynamic Impedance Z <sub>ZK</sub> (Ω) <sup>Note 2</sup>		Reverse Current I <sub>R</sub> (μA)	
		MIN.	MAX.	I <sub>Z</sub> (mA)	MAX.	I <sub>Z</sub> (mA)	MAX.	I <sub>Z</sub> (mA)	MAX.	V <sub>R</sub> (V)
RD11ES	AB	10.18	11.26	5	20	5	120	0.5	0.2	8.0
	AB1	10.18	10.63							
	AB2	10.50	10.95							
	AB3	10.82	11.26							
RD12ES	AB	11.13	12.30	5	25	5	110	0.5	0.2	9.0
	AB1	11.13	11.63							
	AB2	11.50	11.92							
	AB3	11.80	12.30							
RD13ES	AB	12.18	13.62	5	25	5	110	0.5	0.2	10
	AB1	12.18	12.71							
	AB2	12.59	13.16							
	AB3	13.03	13.62							
RD15ES	AB	13.48	15.02	5	25	5	110	0.5	0.2	11
	AB1	13.48	14.09							
	AB2	13.95	14.56							
	AB3	14.42	15.02							
RD16ES	AB	14.87	16.50	5	25	5	150	0.5	0.2	12
	AB1	14.87	15.50							
	AB2	15.33	15.96							
	AB3	15.79	16.50							
RD18ES	AB	16.34	18.30	5	30	5	150	0.5	0.2	13
	AB1	16.34	17.06							
	AB2	16.90	17.67							
	AB3	17.51	18.30							
RD20ES	AB	18.14	20.45	5	30	5	200	0.5	0.2	15
	AB1	18.14	18.96							
	AB2	18.80	19.68							
	AB3	19.52	20.45							
RD22ES	AB	20.23	22.61	5	30	5	200	0.5	0.2	17
	AB1	20.23	21.08							
	AB2	20.76	21.65							
	AB3	21.22	22.09							
	AB4	21.68	22.61							
RD24ES	AB	22.26	24.81	5	35	5	200	0.5	0.2	19
	AB1	22.26	23.12							
	AB2	22.75	23.73							
	AB3	23.29	24.27							
	AB4	23.81	24.81							
RD27ES	AB	24.26	27.64	5	45	5	250	0.5	0.2	21
	AB1	24.26	25.52							
	AB2	24.97	26.26							
	AB3	25.63	26.95							
	AB4	26.29	27.64							
RD30ES	AB	26.99	30.51	5	55	5	250	0.5	0.2	23
	AB1	26.99	28.39							
	AB2	27.70	29.13							
	AB3	28.36	29.82							
	AB4	29.02	30.51							
RD33ES	AB	29.68	33.11	5	65	5	250	0.5	0.2	25
	AB1	29.68	31.22							
	AB2	30.32	31.88							
	AB3	30.90	32.50							
	AB4	31.49	33.11							
RD36ES	AB	32.14	35.77	5	75	5	250	0.5	0.2	27
	AB1	32.14	33.79							
	AB2	32.79	34.49							
	AB3	33.40	35.13							
	AB4	34.01	35.77							
RD39ES	AB	34.68	38.52	5	85	5	250	0.5	0.2	30
	AB1	34.68	36.47							
	AB2	35.36	37.19							
	AB3	36.00	37.85							
	AB4	36.63	38.52							

Notes 1. tested with pulse (40 ms)

2. Z<sub>Z</sub> and Z<sub>ZK</sub> are measured at I<sub>Z</sub> by given a very small A.C. current signal.

3. Suffix AB is Suffix AB1, AB2, AB3 or AB4.

TYPICAL CHARACTERISTICS (T<sub>A</sub> = 25°C)

Fig. 1 ZENER CURRENT vs. ZENER VOLTAGE




Fig. 2 ZENER CURRENT vs. ZENER VOLTAGE




Fig. 3 ZENER CURRENT vs. ZENER VOLTAGE




Fig. 4 ZENER CURRENT vs. ZENER VOLTAGE







Fig. 5 ZENER CURRENT vs. ZENER VOLTAGE




**Fig. 6 POWER DISSIPATION vs. AMBIENT TEMPERATURE**




**Fig. 7 THERMAL RESISTANCE vs. SIZE OF P.C. BOARD**



**Fig. 8 DYNAMIC IMPEDANCE vs. ZENER CURRENT**



**Fig. 9 ZENER VOLTAGE TEMPERATURE COEFFICIENT vs. ZENER VOLTAGE**



**Fig. 10 SURGE REVERSE POWER RATINGS**





Fig. 11 TRANSIENT THERMAL IMPEDANCE CHARACTERISTIC



- **The information in this document is current as of April, 2003. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets or data books, etc., for the most up-to-date specifications of NEC Electronics products. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.**
- No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC Electronics products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of a customer's equipment shall be done under the full responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality, reliability and safety of NEC Electronics products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC Electronics products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment and anti-failure features.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and "Specific".

The "Specific" quality grade applies only to NEC Electronics products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.

"Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.

"Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).

"Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

(Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).