



Xbee Pro RF Modules 928MHz 200Kbps 20-Pin w& Cortex-M3 EFM32G230 @28MHz - XBP9B-DMWT-022

SKU 113990076



1 [ADD TO CART](#)

Description

XBee-PRO 900HP embedded modules provide best-in-class range wireless connectivity to devices. They take advantage of the DigiMesh® networking protocol, featuring dense network operation and support for sleeping routers, and are also available in a proprietary point-to-multipoint configuration.

Supporting RF line-of-sight ranges up to 28 miles (with high-gain antennas), and data rates of up to 200 Kbps, these modules are ideal for extended-range applications requiring increased data throughput.

The XBee-PRO 900HP requires no programming and can be configured easily using Digi's free X-CTU software or via a simplified AT command set. XBee modules are pre-certified for use in multiple countries, further reducing development costs and time to market.

XBee® modules are easy to use, share a common hardware footprint and are available in a variety of different protocols, enabling users to substitute one XBee for another with minimal development time and risk.

- Perior outdoor LOS range of up to 28 miles with high-gain antenna
- Simplified AT command set or advanced XBee API accelerates time to market
- Over-the-air firmware updates via other XBee-PRO 900HP modules or Device Cloud by Etherios™
- Software-selectable channel mask for interference immunity
- Advanced sleep modes include sleeping routers, pin sleep, cyclic sleep

HARDWARE

- Processor: ADF7023 transceiver, Cortex-M3 EFM32G230 @ 28 MHz
- Frequency Band: 902 to 928 MHz, software selectable channel mask for interference immunity
- Antenna Options: Wire, U.FL and RPSMA
- RF Data Rate: 10 Kbps or 200 Kbps
- Indoor/Urban Range: 10 Kbps: up to 2000 ft (610 m); 200 Kbps: up to 1000 ft (305 m)
- Outdoor/ Line-Of-Sight Range : 10 Kbps: up to 9 miles (14 km); 200 Kbps: up to 4 miles (6.5 km) (w/ 2.1 dB dipole antennas)
- Transmit Power: Up to 24 dBm (250 mW) software selectable
- Receiver Sensitivity: -101 dBm @ 200 Kbps, -110 dBm @ 10 Kbps
- Data Interface: UART (3V), SPI
- GPIO: Up to 15 Digital I/O, 4 10-bit ADC inputs, 2 PWM outputs
- Networking Topologies: DigiMesh, Repeater, Point-to-Point, Point-to-Multipoint, Peer-to-Peer
- Spread Spectrum: FHSS (Software Selectable Channels)
- Supply Voltage: 2.1 to 3.6 VDC
- Transmit Current: 215 mA
- Receive Current: 29 mA
- Sleep Current: 2.5 uA

Technical Details

Dimensions	50mm x 70mm x 7.70mm
Weight	G.W 5g
Battery	Exclude

ECCN/HTS

ECCN Not Available
HSCODE8517709000

Questions and Answers

Have a question about this? Ask people who



Xbee Pro RF Modules 928MHz 200Kbps 20-Pin w& Cortex-M3 EFM32G230 @28MHz - XBP9B-DMWT-022

SKU 113990076



IN STOCK
16 Available

1

ADD TO CART

- Description
- Technical Details
- Questions and Answers
- <>
- ×

×

Notify me when it's back in stock

Please enter a valid email address

SUBMIT

^

POPULAR SEARCHES

- PCB Manufacturing
- PCB Assembly
- PCB Layout
- 3D Printing
- PCB Stencil
- Lora
- ReSpeaker
- Grove
- Lidar
- GPS
- Can-Bus
- Arduino
- Arduino Shield
- Beaglebone
- Raspberry Pi
- FPGA
- LinkIt ONE
- Crazyflie 2.0
- Raspberry Pi 3 Model B
- RF Explorer
- DSO Nano v3
- HiKey
- rplidar
- raspberry pi relay
- RPLIDAR A2

Company

- About Seeed
- Distributors
- Careers
- Contacts

Help Center

- How to Get Help
- FAQ
- Technical Support
- Shipping & Order
- Warranty & Returns
- Payment Information

Community

- Project Hub
- Forum
- Blog
- Wiki

Stay Tuned

Subscribe to our newsletter.

email address

>



PayPal

VISA

Select Language

Contact Support