HellermannTyton

Technical data sheet

Article number:
300-30123 HIS-PACK-1.2/0.6



Product Group	Heat shrinkable tubing 2:1 on a reel
Product Family	HIS-PACK
Material	Polyolefin, cross-linked (PO-X)
Colour	Transparent (CL)

Behaviour at Heat Shock	not dripping
Dielectric Strength [Test method]	20 kV/mm [IEC 243]
Elongation at break (min.) [Test method]	800 % [IEC 684 P2]
Heat Aging Test	168h/175°C
Heat Shock Test	4h/250°C
Insulation Class	E (VDE 0530)
Longitudinal Change After Shrinkage	+/-5%
Min. Shrink Temperature - °C	+100 °C
Operating Temperature	-55 °C to +125 °C
Package Content	10 m
Package Content packed in	pcs.
Recov. Ø d max.	0.6 mm
Shrink Ratio	2:1
Supplied Ø D min.	1.2 mm
Tensile Strength	17 MPa
Wall (WT)	0.40 mm
Water Absorption	0.15 %

HF ✓ RoHS ✓

created on 15. May 2026, 4:36 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.