

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2016



© COPYRIGHT 2016

BY TE CONNECTIVITY



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI5850	21DEC1998	-	RDR
	A	REVISED PER E.O. PI9446	15JAN2007	-	RDR
	B	REVISED PER E.O. P20338	5NOV2009	-	RDR
	C	REVISED PER PCN-24-222744	18SEP2024	GB	CB



MODIFICATION
IDENTIFICATION
NUMBER



DATE CODE : MONTH REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS.
EX. A = JANUARY
YEAR IS REPRESENTED BY LAST NUMERICAL DIGIT
EX. 0 = 2020

TE INTERNAL PN	DEUTSCH PN
DT06-3S-EP09	DT06-3S-EP09

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm ²] REF. ONLY
16	.088 [2.23]	.145 [3.68]	14-20 AWG [2.5-0.5]

3 MATERIAL: HOUSING: PA66 GF15 (BLACK)
CAP: PA66 GF15 (BLACK)
FRONT SEAL: VMQ (RED-ORANGE)
GROMMET: VMQ (RED-ORANGE)


2. THIS PLUG MATES WITH DT04-3P-XXXX RECEPTACLE.
(XXXX = ALL MODIFICATIONS)
CONSULT FACTORY FOR MODIFICATION

1 FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS, SEE ENVELOPE DRAWINGS 0425-015-000
AND 0425-017-0000

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
in [mm]



MATERIAL



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [0.64]
4 PLC ±
ANGLES ±1°

FINISH

DWN S. THEIS 24NOV1998

CHK B. BYFORD 05NOV2009

APVD S. BEARD 04NOV2009

PRODUCT SPEC

108-151009

APPLICATION SPEC

114-151009

WEIGHT

7.10g

CUSTOMER DRAWING



TE Connectivity

NAME
3 WAY PLUG
LATCH PROTECTOR CAP
DT SERIES

SIZE

A3

CAGE CODE

4AFU8

DRAWING NO

DT06-3S-EP09

RESTRICTED TO

SCALE

3:1

SHEET

1 OF 1

REV

C