




STYLE U





EXTENDED JACKSCREW OPTION
SEE TABLE 1



STYLE Z

STYLE N

STYLE F



DRAWN K-K-W		DATE 23/11/2017		3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: BTMM SERIES				 Polamco			
APPROVED BY M. PAUL		23/11/2017			TITLE: MICRO MIN BANDING BACKSHELL							
CHECKED BY K. SHEPPARD		24/11/2017										
DOC TYPE Customer Drawing			UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°		ASSY USED ON: TO FIT MIL-DTL-83513 CONNECTORS					RESTRICTED TO:		
ISSUE/REV AB		DCR ---										
NCAGE CODE U5792		WEIGHT N/A	MATERIAL SEE PART NUMBER BREAKDOWN		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.				POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT 1	DRAWING NO: P10380
FINISH SEE PART NUMBER BREAKDOWN												

Downloaded from Arrow.com

TABLE 1

SHELL SIZE	A	B	C	MAX ENTRY	MAX ENTRY BACKSHELL WITH 'EK' HARDWARE OPTION	MIN LENGTH CODE** U & Z
09	19,68	14,35	9,0	04	03*	L13
15	23,50	18,16	9,0	05	04	L13
21	27,30	21,97	9,0	06	05	L13
25	29,84	24,51	9,0	07	06	L13
31	33,66	28,32	9,0	07	06	L13
37	37,46	32,13	9,0	08	07	L13
51	36,20	30,86	10,0	08	07	L13
100	54,86	45,72	11,0	11	08	L16

TABLE 2

ENTRY SIZE	D	E	F	N	M
01	26,0	1,6	1,6	17,38	24,74
02	26,0	3,2	3,2	18,52	25,88
03	26,0	4,8	4,8	19,65	27,01
04	26,4	7,0	5,8	21,02	28,56
05	30,2	10,8	5,8	23,89	31,25
06	34,6	15,2	5,8	27,00	34,21
07	39,5	17,9	6,5	30,47	37,83
08	42,2	22,8	6,8	34,12	40,61
09	43,9	26,0	7,4	35,95	42,66
11	55,2	35,8	8,4	41,57	48,93

* EXCEPTION: 09-04 AVAILABLE WITH 'EK' FOR LENGTH CODE L8
** FOR 09-04 LENGTH CODE L8 IS AVAILABLE,
FOR 15-05 LENGTH CODE L11 IS AVAILABLE.

TABLE 3


CODE	MATERIAL / FINISH
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
1-CHP	ALUMINIUM / ELECTROLESS NICKEL, HIGH PHOSPHOR
1-Y	ALUMINIUM / YELLOW CHROMATE OVER CADMIUM

SEE WEBSITE FOR FULL LIST AND SPECS OF MATERIALS AND FINISHES.

BTMM-U-21-06-1-C-SL

SERIES _____
STYLE _____
SHELL SIZE (TABLE 1) _____
ENTRY SIZE (TABLE 2) _____
INSERT 'T' FOR QWIK-TY OPTION _____
OMIT FOR STANDARD ENTRY _____
MATERIAL (TABLE 3) _____
FINISH (TABLE 3) _____
INSERT -Lxx FOR NONSTANDARD LENGTH _____
xx - LENGTH IN MM TO THE SHOULDER
OMIT FOR STANDARD LENGTH*** _____
SCREW REF.
SL - SLOT HEAD JACKSCREW
SK - SOCKET HEAD JACKSCREW
FSL - FLOATING SLOT HEAD JACKSCREW
FSK - FLOATING SOCKET HEAD JACKSCREW
EK - EXTENDED JACKSCREW

QWIK-TY OPTION



*** STANDARD LENGTHS ARE:
- 15,00MM FOR STYLE U,
- 20,00MM FOR STYLE Z,
- SEE TABLE 2 FOR STANDARD LENGTHS FOR STYLES N & F,
- MINIMUM LENGTHS AS PER TABLE 1 FOR STYLES U & Z,
- FOR STYLES N & F STANDARD LENGTHS ARE THE MINIMUM LENGTHS,
- FOR MAX LENGTHS CONSULT ENGINEERING.

DRAWN K-K-W		DATE 23/11/2017			PART NUMBER: BTMM SERIES							
APPROVED BY M.PAUL		23/11/2017			TITLE: MICRO MIN BANDING BACKSHELL							
CHECKED BY K.SHEPPARD		24/11/2017		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/- 0.25MM ANGULAR +/- 1°	ASSY USED ON: TO FIT MIL-DTL-83513 CONNECTORS				RESTRICTED TO: POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT 2	DRAWING NO: P10380
DOC TYPE Customer Drawing												
ISSUE/REV AB		DCR ---		MATERIAL SEE PART NUMBER BREAKDOWN	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.							
NCAGE CODE U5792		WEIGHT N/A										