

MICRO SWITCHFREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH-BASIC**

CATALOG LISTING

BA-1RV5435246-A2**BA-1RV5435246-A2**

PAGE 1 OF 1

DRAWING
NUMBER

5

ISSUE

RELEASE NO. PR-11436T REPLACES X 71636-B A

CHECK

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	CO-7758R	MAM	29 MAR 94
C	CO93346	DLT	31 AUG 98
D	CO93921	GJW	13 JAN 99

CHECK

10 A/C 32


CER

82 CHECK

D J S 6 AUG 82

FORMTEK


FD-52848-A

**NOTES**MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ----- 1.5 OZ MAX

RELEASE FORCE ----- 1/2 OZ MIN

DIFFERENTIAL TRAVEL ----- .030 MAX

OVERTRAVEL ----- .060 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T

CODE L65

15A-125, 250 OR 480 VAC
1/2HP-125 VAC, 1HP-250 VACL288
L299
L306
16A 250V ~ T85 5E4**SCALE FULL**

DO NOT SCALE PRINT

TOLERANCESAPPLY TO DESIGN UNITS - CONVERSIONS ARE ONLY FOR
REFERENCE - UNLESS NOTED - TOLERANCES ARE 2

NO PLACES	DIM	TOL	DIM	TOL
ONE PLACE	X	1/64	X	0.01
TWO PLACES	X, X	0.001	X, X	0.001
THREE PLACES	X, X, X	0.0001	X, X, X	0.0001

DESIGN UNITS ☐ METRIC ☒ US CUSTOMARY

WEIGHT .063 LB