


By Burndy
Catalog # [BIT4](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided
Entry, 14-4 AWG, Al/Cu Rated



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

EU RoHS Indicator	Yes
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - UL Listed Direct Burial	No
Buy American Compliant	Yes
Buy America(n) Qualified	Buy America Compliant (All status valid till December 2025);Buy American Act Compliant (All status valid till December 2025);BABA Compliant (All status valid till December 2025);TAA Compliant (All status valid till December 2025)

Conductor

Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Type	AL C Str-Size;CU C Str-Size
Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	14 AWG - 4 AWG

Configuration

Physical Attribute - Number of Screws	2
---------------------------------------	---

Number Of Ports	2
-----------------	---

Current

Voltage - Maximum	600 V
Operating Voltage	600 V

Dimensions

Dimension - Width inch	1.16 in
Dimension - Width mm	29 mm
Dimension - Height inch	1.25 in
Dimension - Height mm	32 mm
Dimension - Width fraction	1-4/25 in

Force Related

Installation Torque Recommended in-lb	45 in-lb
---------------------------------------	----------

General

Sub Brand	UNITAP
Material - Hardware	Aluminum
Physical Attribute - Screw Type	Allen
Insulation Type	Plastisol
Trade Name	UNITAP™
Type	BIT
UPC 12 Digit	781810134146
UPC 14 Digit GTIN	00781810134146
Material	Aluminum
Hex Key	1/8 in
UPC	781810134146

Logistics

Carton Quantity	250
Minimum Pack Quantity	1

Operational

Temperature Rating	90 °C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)