OMRON Industrial Automation



MY4-GS-R AC110/120

Relay, plug-in, 14-pin, 4PDT, 6 A, mechanical indicator, 100/110 VAC

Downloaded from Arrow.com.

Specifications

Mounting method	With plug-in socket
Usage	General purpose
Poles	4
Rated carry current	6 A
Coil voltage	110 V
Operation voltage	AC
Contact material	Ag
Contact description	4PDT
Features	Transparent case, With mechanical indicator
Terminal type	Plug-in, Solder

Downloaded from Arrow.com.

Fits to



PY14-02 FOR MY
Socket, back-connecting, 14-pin, PCB terminals



PYF-14-PU BY OMB
Socket, DIN rail/surface mounting, 31 mm, 14-pin, Push-in terminals



PYF-14-PU-L BY OMB
Socket, DIN rail/surface mounting, 31 mm, 14-pin, Push-in terminals,



PYF14-ESN-B
Socket, with common and coil terminals on the bottom and with the NC & NO terminal on the top - Black.



PYF14-ESS-B
Socket, with coil terminals on the bottom and with the common and NC & NO terminals on the top - Black.



PYF14A-N BY OMZ
Socket, DIN rail/surface mounting, 14-pin, screw terminals (IEC/VDE)



PYF14S BY OMZ
Socket, DIN rail mounting, 14-pin, screwless terminals



PYFZ-14-E BY OMZ
Socket, DIN rail/surface mounting, 14-pin, screw terminals (standard)

Downloads



Industrial Relays
Brochure
EN PDF 2.77 MB



MY-GS-R/MY(s)/MYK/MYQ/MYH Miniature Power Relays
Datasheet
EN PDF 20.3 MB



OMRON Manufacturing Know-How: High Quality Relays
Leaflet
EN PDF 449 KB



Panel Building
Brochure
EN PDF 3.11 MB



Solution case study No.8 Environment resistance
Brochure
EN PDF 623 KB

Downloaded from Arrow.com.

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 11 September, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.