





Similar to illustration



Features:

- Space-saving ECB with four channels
- Nominal current: 2 ... 10 A (adjustable for each channel via sealable selector switch); Factory preset: 2 A (when switched off)
- Switch-on capacity > 50000  $\mu$ F per channel
- One illuminated, three-colored button per channel simplifies switching (on/off), resetting, and on-site diagnostics
- Time-delayed switching of channels
- Tripped and switched off message (common group signal) via isolated contact, ports 13 / 14
- Remote input resets all tripped channels

Technical data			
Input		Output	
Nominal input voltage $U_{in\,nom}$	24 VDC	Total number of channels (module)	4
Input voltage range	18 ... 30 VDC	Nominal output voltage $U_{o\,nom}$	4 x 24 VDC
		Output voltage range	18 ... 30 VDC ( $U_e$ – voltage drop)
		Voltage drop	$\leq 200$ mV (10 A) (Input (+))
		Nominal output current $I_{o\,nom}$	4 x 2 / 3 / 4 / 6 / 8 / 10 A (adjustable for each channel via selector switch)
		Default Setting	DC 2 A; switched off
		Trip time	16 ms ... 100 s (load-dependent)
		Switch-on capacity	
		Switch-on behavior	Time-delayed channel switching (load-dependent, min. 50 ms / max. 5 s)
		Active current limitation	No
		Current limitation	No



Signaling and communication	
Signaling	4 x LED (green/red/orange) 1 x Remote control input (S1) 1 x Group signal contact (13; 14)
Operation status indicator	Green LED (channel OK) Red LED (tripped channel)
Remote input	Reactivation of all tripped channels via 15 ... 30 VDC pulse for min. 500 ms

Circuit protection	
Internal fuse	T 15 A per channel

Safety and protection	
Isolation voltage (connectors – housing)	0.5 kVDC
Protection class	III
Protection type	IP20; per EN 60529
Reverse voltage protection	No
Resistance to reverse feed	≤ 35 VDC
Pollution degree	2
Transient suppression (primary)	Suppressor diode (33 V)
Parallel operation of single channels	Not permitted
Series operation	No
MTBF	> 500,000 h (per IEC 61709)

Connection data			
Connection 1		Connection 2	
Connection type	Input (+)	Connection type	Input (–); output; signaling
Connection technology	Push-in CAGE CLAMP®	Connection technology	CAGE CLAMP®
WAGO connector	WAGO 831 Series	WAGO connector	WAGO 721 Series
Solid conductor	0.5 ... 10 mm² / 20 ... 8 AWG	Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.5 ... 10 mm² / 20 ... 8 AWG	Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length	13 ... 15 mm / 0.51 ... 0.59 inches	Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data	
Width	45 mm / 1.772 inches
Height	90 mm / 3.543 inches
Depth from upper-edge of DIN-rail	115.5 mm / 4.547 inches

Mechanical data	
Mounting type	DIN-35 rail



Material data		
Fire load		0.733 MJ
Weight		170 g

Environmental requirements		
Ambient temperature (operation)		-25 ... +70 °C
Ambient temperature (storage)		-25 ... +85 °C
Relative humidity		5 ... 96 % (no condensation permissible)
Derating		≥ 50 °C (see instruction manual)

Standards and specifications		
Conformity marking		CE
Standards/specifications		EN 61000-6-2 EN 61000-6-3 UL 508 UL 2367 DNV

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
Customs tariff number		85363010000

Product classification		
UNSPSC		39121601
eCl@ss 10.0		27-37-18-02
eCl@ss 9.0		27-37-18-02
ETIM 9.0		EC001440
ETIM 8.0		EC001440
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Approvals / Certificates		
General approvals		Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-



Approvals for marine applications



Approval	Standard	Certificate Name
DNV DNV GL SE	-	TAA0000281

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 787-1664/000-054



Documentation

Bid Text
787-1664/000-054
03.07.2019
xml 6.88 KB
787-1664/000-054
02.07.2019
docx 20.58 KB



Instruction Leaflet
Elektronische Schutz- schalter
pdf 590.18 KB



Application Notes

Application Note e!COCKPIT
e!COCKPIT Application
Note WagoAppFuse
(a2019001)
2021-11-08
06.12.2021
pdf 548.17 KB



CAD/CAE-Data

CAD data
2D/3D Models
787-1664/000-054



CAE data
EPLAN Data Portal
787-1664/000-054
WSCAD Universe
787-1664/000-054
ZUKEN Portal
787-1664/000-054





1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marker



**Item No.: 2009-145**  
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



**Item No.: 248-501**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



**Item No.: 793-5501**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



**Item No.: 793-501**  
WMB marking card; as card; not stretchable; plain; snap-on type; white



**Item No.: 2009-115**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.1.2 Marking strip



**Item No.: 2009-110**  
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white



**Item No.: 210-831**  
Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white



**Item No.: 210-832**  
Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

1.1.2 Tool

1.1.2.1 Operating tool



**Item No.: 210-720**  
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured



**Item No.: 210-721**  
Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured



**Item No.: 210-769**  
SCREWDRIVER; green