Part Number : 1710888411
Product Description : EXTreme Ten60Power Right-Angle Plug with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail
Series Number : 171088
Status : Active
Product Category : Board-to-Board Connectors
Engineering Part Number : 171088-8401



Documents and Resources

Drawings

1710888411_sd.pdf

1710888411_stp.zip

Symbol and Footprint (Multi-Format)

Specifications

PS-171088-0000-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:a8b6af20-e731-45d8-9f93-e8688a3aac82
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	171088
Description	EXTreme Ten60Power Right-Angle Plug with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail
Application	Board-to-Board, Power, Signal
Component Type	PCB Header, Plug
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	195842726888

Agency

CSA	LR19980

Electrical

Current - Maximum per Contact	2.5A, 30.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16

Downloaded from Arrow.com.

Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	10.00mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	8.738/g
Number of Rows	1, 5
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.58mm
PC Tail Length	2.50mm, 3.28mm
Pitch - Mating Interface	2.00mm, 8.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	1sp - 15s
Shrouded	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Ten60Power Vertical	1710898411

Downloaded from Arrow.com.

Receptacle with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail	
EXTreme Ten60Power Right-Angle Receptacle with Guides, 1 Split Power Circuit, 15 Signal Circuits, Press Fit Tail	1710908411

Downloaded from Arrow.com.