

CATALOG LISTING

121EN93-2

PAGE 1 OF 1

RELEASE NO.

SR-10642

REPLACES

DRAWING NUMBER

M

ISSUE

20

REVISIONS

A	CO44351	
12	WJM	FEB 80
B	CO47573	PRT 4
14	RJH	AUG 80
C	CO 57370	
14	WJM	MAY 85
D	CO 67176	
20	MAM	APR 90
E	CO74101	
30	GJW	JAN 93
F	CO 77804	SAB
16	WJM	MAY 94
G	201514	
24	CSL	OCT 00
H	0006608	
21	KR	JUL 04

WJM

12 FEB 80

WJM

14 FEB 80

WJM

12 FEB 80

WJM




14 FEB 80

WJM

12 FEB 80

WJM

14 FEB 80



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - ③ TO ADJUST ROLLER DIRECTION REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
 - 4 - NOTED ELECTRICAL RATINGS APPLY AS SPECIFIED IN MIL-PRF-8805/43 UP TO 185°F
 - 5 - CIRCUIT DIAGRAM, CATALOG LISTING, AND DATE CODE ARE SHOWN ON NAMEPLATE
 - 6 - REPLACEMENT LOCK RING - PACKET 15PA137
 - ⑦ - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION		SCALE FULL	
CHARACTERISTICS		ELECTRICAL DATA		DO NOT SCALE PRINT	
OPERATING FORCE ----- 6-12 LB		CONTACT ARRANGEMENT		TOLERANCES	
FULL OVERTRAVEL FORCE ----- 30 LB MAX		SPDT (2)		APPLY TO DESIGN UNITS CONVERSIONS ARE ONLY FOR REFERENCE UNLESS NOTED TOLERANCES ARE ±	
RELEASE FORCE ----- 4 LB MIN		28 VDC		NO PLACES	DM TOL
PRETRAVEL ----- .040 MAX		SEA LEVEL		ONE PLACE	DM TOL
DIFFERENTIAL TRAVEL ----- 020 MAX		50,000 FT.		TWO PLACES	DM TOL
OVERTRAVEL ----- .250 MIN		LAMP		THREE PLACES	DM TOL
				ANGLES	DM TOL
				DESIGN UNITS	BI METRIC
				RAW MATERIAL - COMMERCIAL STANDARD	
				MICRO SWITCH STANDARDS APPLY	
				DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED	
				WEIGHT 4.7 OZ MAX	