




[+ HARNESSING](#)
[HEAT SHRINK BOOTS](#)



✓ Active

TE CONNECTIVITY (TE)
202A185-25/86-0
[Raychem](#) | [CAP](#) , [CRPS](#)

202A185-25/86-0
TE Internal Number: 414167-000
Alias ID: 2-1193122-8

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Lipped No

Operating Temperature Range (°C) -55 – 105

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Material Systems Code 25

[↓](#) **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Boot, Straight, Overexpanded
PDF
English

Product Specifications

Product Specification

Thermofit Elastomeric Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable
PDF
English

-25 MOULDED PARTS
PDF
English

Product Environmental Compliance

Safety Data Sheet

Aliphatic Polyamide Based Adhesives.

PDF

Dutch

Aliphatic Polyamide Based Adhesives.

PDF

English

Aliphatic Polyamide Based Adhesives.

PDF

French

Aliphatic Polyamide Based Adhesives.

PDF

German

Aliphatic Polyamide Based Adhesives.

PDF

Italian

Aliphatic Polyamide Based Adhesives.

PDF

Spanish

Aliphatic Polyamide Based Adhesives.

PDF

Swedish

Aliphatic Polyamide Based Adhesives.

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF
Spanish

EPS Heat Shrinkable Polymeric Products

PDF
Swedish

EPS Heat Shrinkable Polymeric Products

PDF
Dutch

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped No

Body Features

Material Systems Code 25

Adhesive Pre-Coat Yes

Material Modified Elastomer

Dimensions

Cable Diameter Range 19.6 – 54.1 mm [.772 – 2.13 in]

Wire/Cable Outside Diameter .87 in, .9 in, .94 in, 1 in, 1.02 in, 1.1 in, 1.18 in, 1.26 in, 1.34 in, 1.42 in, 22 mm, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 34 mm, 36 mm

Usage Conditions

Operating Temperature Range (°C) -55 – 105

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No

Approved Standards BS-G-198-5-DE, DEF Std 59-97 Issue 3 Type DE, IEC 62329-3-102, MIS-34867

Other

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options /86 Precoat, -55 – 105°C (-67 – 221°F)

Adhesive Type High Performance Pre-Coat Adhesive

Statement of Compliance

Statement of Compliance

PDF