



Find Honeywell product info in one mouse click:
Datasheets, virtual tour, images, partnumbers, ...


[Home](#) > [Products](#) > [2D Scanners](#) > [Voyager 1450g/1452g Upgradeable](#)

Voyager 1450g/1452g Upgradeable



Download



Cookie Control

This site uses cookies to store information on your computer.

[read more](#)

The Voyager **1450g** allows enterprises to embrace area-imaging at their own pace, and in the most cost-effective manner. Built on the platform of Honeywell's world-renowned Voyager series of handheld scanners, the Voyager 1450g delivers omnidirectional reading of linear bar codes, plus the ability to affordably upgrade the device to enable PDF and 2D bar code scanning—either at the time of purchase, or as data capture needs evolve.

The Voyager **1452g** allows enterprises to embrace area-imaging at their own pace, and in the most cost-effective manner. Built on the platform of Honeywell's world-renowned Voyager series of handheld scanners, the Voyager 1452g delivers omnidirectional reading of linear bar codes, plus the ability to affordably upgrade the device to enable PDF and 2D bar code scanning—either at the time of purchase, or as data capture needs evolve. Incorporating a Bluetooth® Class 2 radio, the Voyager 1452g has a wireless range of up to 10 meters (33 feet) from the base.

Specifications

Reliable Data Collection: Offers omnidirectional reading of virtually all linear bar codes and the most widely used 2D bar codes, including poor quality and mobile bar codes (2D decoding available in select models).

Go Beyond 1D Codes: Unlike traditional laser scanners, the 1D version of Voyager 1450g / 1452g can read bar codes omni-directionally, making it ideal for presentation scanning.

Mobile Phone Reading: Scans coupons, mobile tickets and digital wallets from the screens of mobile devices.

Future Proof: For those who only require 1D scanning now but anticipate the need for 2D scanning in the future, the Voyager 1450g / 1452g can be affordably upgraded from 1D to 2D scanning at any time.

Flexible Licensing Solution: Meets diverse scanning requirements by offering models with basic functionality, with software licenses enabling additional functionality as needs evolve.

Kit

1450g1D-2USB USB Kit: Omni-directional, 1D, black scanner (1450g1D-2), USB Type A 1.5m straight cable (CBL-500-150-S00)

1450g1D-2USB-1 USB Kit: Omni-directional, 1D, black scanner (1450g1D-2), flexible presentation stand (STND-15F03-009-4), USB Type A 1.5m straight cable (CBL-500-150-S00)

1450g2D-1USB USB Kit: Omni-directional, 1D, PDF, 2D, ivory scanner (1450g2D-1), USB Type A 1.5m straight cable (CBL-500-150-S00),

1450g2D-1USB-1 USB Kit: Omni-directional, 1D, PDF, 2D, ivory, scanner (1450g2D-1), flexible presentation stand (STND-15F03-009-4), USB Type A 1.5m straight cable (CBL-500-150-S00)

1450g2D-2USB USB Kit: Omni-directional, 1D, PDF, 2D, black scanner (1450g2D-2), USB Type A 1.5m straight cable (CBL-500-150-S00)

1450g2D-2USB-1 USB kit: Omni-directional, 1D, PDF, 2D, black scanner (1450g2D-2), flexible presentation stand (STND-15F03-009-4), USB Type A 1.5m straight cable (CBL-500-150-S00)

1452g1D-2USB-5 USB Kit: Omni-directional, 1D, black scanner (1452g1D-2), charge & communication base (CCB01-010BT-V7N), USB Type A 3.0m straight cable (CBL-500-300-S00)

1452g2D-2USB-5 USB Kit: Omni-directional, 1D, PDF,2D, black scanner (1452D-2),charge & communication base (CCB01-010BT-V7N), USB Type A 3.0m straight cable (CBL-500-300-S00)

Scanner Only - cable sold separately



Cables



Stands/Holders/Cordless Bases/Access Points



Power & Charger



Software



Service & Repair - Scanner Service Contracts



Sitemap

[Home](#)
[Products](#)
[Promotions](#)
[News](#)
[Grow your Business](#)
[Contact](#)
[Order Now](#)
[Scansource Europe](#)
[Honeywell](#)
[Terms of Use](#)
[Webdesign by Blue4You](#)

Contact

Call your local freephone number to get in touch with a ScanSource Europe Account Manager. Click the button below to find the overview of the available ScanSource Europe freephone numbers.

[► Freephone numbers](#)

© Copyright 2012 ScanSource Honeywell