

KMQ Series




- Downsized from current standard KMG series
- Solvent resistant type except 160 to 450V_{dc}
(see PRECAUTIONS AND GUIDELINES)
- RoHS2 Compliant

SPECIFICATIONS

Items	Characteristics													
Category	-55 to +105°C(6.3 to 100V _{dc}) -40 to +105°C(160 to 400V _{dc}) -25 to +105°C(450V _{dc})													
Temperature Range														
Rated Voltage Range	6.3 to 450V _{dc}													
Capacitance Tolerance	±20% (M) (at 20°C, 120Hz)													
Leakage Current	6.3 to 100V _{dc}						160 to 450V _{dc}							
	I=0.03CV or 4µA, whichever is greater.						CV≤1,000		I=0.1CV+40 max.					
							CV>1,000		I=0.04CV+100 max.					
Where, I : Max. leakage current (µA), C : Nominal capacitance (µF), V : Rated voltage (V) (at 20°C after 1 minute)														
Dissipation Factor (tan δ)	Rated voltage (V _{dc})	6.3V	10V	16V	25V	35V	50V	63V	100V	160 to 250V	350 to 400V	450V		
	tan δ (Max.)	0.28	0.24	0.20	0.16	0.14	0.12	0.10	0.08	0.20	0.24	0.24		
	When nominal capacitance exceeds 1,000µF, add 0.02 to the value above for each 1,000µF increase. (at 20°C, 120Hz)													
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (V _{dc})	6.3V	10V	16V	25V	35V	50V	63 to 100V	160 to 200V	250V	350V	400V	450V	
	Z(-25°C)/Z(+20°C)	5	4	3	2	2	2	2	3	3	4	4	6	
	Z(-40°C)/Z(+20°C)	10	8	6	4	3	3	3	4	4	6	6	—	
(at 120Hz)														
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for 2,000 hours at 105°C.													
	Capacitance change	≤ ±20% of the initial value												
	D.F. (tan δ)	≤200% of the initial specified value												
	Leakage current	≤The initial specified value												
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.													
	Rated voltage	6.3 to 100V _{dc}						160 to 450V _{dc}						
	Capacitance change	≤ ±20% of the initial value						≤ ±20% of the initial value						
	D.F. (tan δ)	≤200% of the initial specified value						≤200% of the initial specified value						
	Leakage current	≤The initial specified value						≤500% of the initial specified value						


DIMENSIONS [mm]

- Terminal Code : E



φD	10	12.5	16	18
φd	0.6	0.6	0.8	0.8
F	5.0	5.0	7.5	7.5
φD'	φD+0.5max.			
L'	L+1.5max.			

PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"



◆STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	tan δ	Rated ripple current (mA _{rms} /105°C, 120Hz)	Part No.	WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	tan δ	Rated ripple current (mA _{rms} /105°C, 120Hz)	Part No.	
6.3	2,200	10 × 16	0.30	635	EKMQR3E□□222MJ16S	63	220	10 × 16	0.10	335	EKMQR3E□□221MJ16S	
	3,300	10 × 20	0.32	840	EKMQR3E□□332MJ20S		330	10 × 20	0.10	510	EKMQR3E□□331MJ20S	
	4,700	12.5 × 20	0.34	1,090	EKMQR3E□□472MK20S		470	12.5 × 20	0.10	640	EKMQR3E□□471MK20S	
	6,800	12.5 × 25	0.38	1,350	EKMQR3E□□682MK25S		1,000	16 × 25	0.10	930	EKMQR3E□□102ML25S	
	10,000	16 × 25	0.46	1,650	EKMQR3E□□103ML25S		2,200	18 × 35.5	0.12	1,650	EKMQR3E□□222MMP1S	
	15,000	16 × 31.5	0.56	1,820	EKMQR3E□□153MLN3S		100	68	10 × 12.5	0.08	190	EKMQR3E□□680MJC5S
22,000	18 × 35.5	0.70	2,280	EKMQR3E□□223MMP1S	100	10 × 16		0.08	240	EKMQR3E□□101MJ16S		
10	1,000	10 × 12.5	0.24	460	EKMQR3E□□102MJC5S	220		12.5 × 20	0.08	390	EKMQR3E□□221MK20S	
	2,200	10 × 16	0.26	705	EKMQR3E□□222MJ16S	330		12.5 × 25	0.08	540	EKMQR3E□□331MK25S	
	3,300	12.5 × 20	0.28	1,000	EKMQR3E□□332MK20S	470		16 × 25	0.08	715	EKMQR3E□□471ML25S	
	4,700	12.5 × 25	0.30	1,260	EKMQR3E□□472MK25S	1,000		18 × 35.5	0.08	960	EKMQR3E□□102MMP1S	
	6,800	16 × 25	0.34	1,570	EKMQR3E□□682ML25S	160	68	12.5 × 20	0.20	250	EKMQR3E□□680MK20S	
	10,000	16 × 31.5	0.42	1,820	EKMQR3E□□103MLN3S		100	12.5 × 25	0.20	310	EKMQR3E□□101MK25S	
15,000	16 × 35.5	0.52	2,050	EKMQR3E□□153MLP1S	220		16 × 31.5	0.20	540	EKMQR3E□□221MLN3S		
22,000	18 × 40	0.66	2,420	EKMQR3E□□223MM40S	330		18 × 35.5	0.20	705	EKMQR3E□□331MMP1S		
16	1,000	10 × 12.5	0.20	500	EKMQR3E□□102MJC5S		470	18 × 40	0.20	855	EKMQR3E□□471MM40S	
	2,200	10 × 20	0.22	710	EKMQR3E□□222MJ20S		200	47	12.5 × 20	0.20	195	EKMQR3E□□470MK20S
	3,300	12.5 × 25	0.24	1,170	EKMQR3E□□332MK25S	68		12.5 × 25	0.20	250	EKMQR3E□□680MK25S	
	4,700	16 × 25	0.26	1,500	EKMQR3E□□472ML25S	100		16 × 25	0.20	335	EKMQR3E□□101ML25S	
	6,800	16 × 25	0.30	1,600	EKMQR3E□□682ML25S	220		16 × 35.5	0.20	500	EKMQR3E□□221MLP1S	
	10,000	16 × 35.5	0.38	1,930	EKMQR3E□□103MLP1S	330		18 × 40	0.20	675	EKMQR3E□□331MM40S	
15,000	18 × 40	0.48	2,210	EKMQR3E□□153MM40S	250	47		12.5 × 20	0.20	190	EKMQR3E□□470MK20S	
25	470	10 × 12.5	0.16	380		EKMQR3E□□471MJC5S	68	16 × 25	0.20	270	EKMQR3E□□680ML25S	
	1,000	10 × 16	0.16	610		EKMQR3E□□102MJ16S	100	16 × 25	0.20	310	EKMQR3E□□101ML25S	
	2,200	12.5 × 25	0.18	1,090		EKMQR3E□□222MK25S	220	18 × 35.5	0.20	485	EKMQR3E□□221MMP1S	
	3,300	16 × 25	0.20	1,400		EKMQR3E□□332ML25S	350	22	12.5 × 20	0.24	130	EKMQR3E□□220MK20S
	4,700	16 × 25	0.22	1,570		EKMQR3E□□472ML25S		33	12.5 × 25	0.24	170	EKMQR3E□□330MK25S
	6,800	16 × 35.5	0.26	1,850	EKMQR3E□□682MLP1S	47		16 × 25	0.24	230	EKMQR3E□□470ML25S	
10,000	18 × 40	0.34	2,000	EKMQR3E□□103MM40S	68	16 × 25		0.24	285	EKMQR3E□□680ML25S		
35	330	10 × 12.5	0.14	350	EKMQR3E□□331MJC5S	100		18 × 31.5	0.24	375	EKMQR3E□□101MMN3S	
	470	10 × 16	0.14	460	EKMQR3E□□471MJ16S	400		22	12.5 × 25	0.24	145	EKMQR3E□□220MK25S
	1,000	12.5 × 20	0.14	810	EKMQR3E□□102MK20S		33	16 × 25	0.24	195	EKMQR3E□□330ML25S	
	2,200	16 × 25	0.16	1,260	EKMQR3E□□222ML25S		47	16 × 25	0.24	200	EKMQR3E□□470ML25S	
	3,300	16 × 31.5	0.18	1,500	EKMQR3E□□332MLN3S		68	16 × 31.5	0.24	240	EKMQR3E□□680MLN3S	
	4,700	16 × 35.5	0.20	1,780	EKMQR3E□□472MLP1S		100	18 × 35.5	0.24	310	EKMQR3E□□101MMP1S	
6,800	18 × 40	0.24	2,000	EKMQR3E□□682MM40S	450		22	12.5 × 25	0.24	100	EKMQR3E□□220MK25S	
50	220	10 × 12.5	0.12	300		EKMQR3E□□221MJC5S	33	16 × 25	0.24	125	EKMQR3E□□330ML25S	
	330	10 × 16	0.12	410		EKMQR3E□□331MJ16S	47	16 × 31.5	0.24	155	EKMQR3E□□470MLN3S	
	470	10 × 20	0.12	540		EKMQR3E□□471MJ20S	68	18 × 35.5	0.24	185	EKMQR3E□□680MMP1S	
	1,000	12.5 × 25	0.12	950		EKMQR3E□□102MK25S	100	18 × 40	0.24	200	EKMQR3E□□101MM40S	
	2,200	16 × 31.5	0.14	1,410		EKMQR3E□□222MLN3S						
	3,300	18 × 35.5	0.16	1,770	EKMQR3E□□332MMP1S							

□□ : Enter the appropriate lead forming or taping code.
 *1: Assembly boards with the designated products attached cannot be cleaned.

◆RATED RIPPLE CURRENT MULTIPLIERS

◎Frequency Multipliers

Capacitance(μF)	Frequency(Hz)					
	50	120	300	1k	10k	100k
22 to 68	0.75	1.00	1.25	1.50	1.75	1.80
100 to 1,000	0.80	1.00	1.15	1.30	1.40	1.50
2,200 to	0.85	1.00	1.03	1.05	1.08	1.08

The deterioration of aluminum electrolytic capacitors accelerates their life due to the internal heating produced by ripple current. For details, refer to Section "5-3 Ripple Current Effect on Lifetime" in the catalog, Technical Note.



- Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.
- Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.
- The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.
- The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.
- We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.
- We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products
- We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

[Part Numbering System](#)

[Part Numbering System \(Appendix\)](#)

[Standardization](#)

[Available Items by Manufacturing Locations](#)

[Environmental Measures](#)

[Technical Note](#)

[Precautions and Guidelines](#)

[Recommended Soldering Conditions](#)

[Taping, Lead-preforming and Packaging](#)

[Available Terminals for Snap-in and Screw Mount Type](#)