



NC6FD-LX

6 pole female receptacle, solder cups, Nickel housing, silver contacts

The DLX series features a compact all metal housing with an ingenious duplex ground contact, which offers excellent RF protection and shielding.

Features & Benefits

- ✓ All metal housing offers best overall RF protection and electromagnetic shielding
- ✓ Duplex ground contact for excellent contact integrity between chassis and cable connector
- ✓ Female contact incorporates a solder barrier to prevent solder running into the contact mating area
- ✓ Larger solder contacts for easier termination
- ✓ Optional connection to easily join pin1 to chassis ground
- ✓ D-style housing provides installation compatibility with industry standard D mounting dimensions

Technical Information

Product	
Title	NC6FD-LX
Connection Type	XLR
Gender	female

Electrical

Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	7,5 A
Rated voltage	$< 50 \text{ V}$

Mechanical

Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	max. 1.0 mm^2
Wiresize	max. 18 AWG
Wiring	Solder contacts
Locking device	Latch lock
Chassis shape	D

Material	
Contact plating	2 µm Ag
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Steel Ck67
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel

Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C