

# Product data sheet

Specifications

## Power Cord, C13 to C14, 2.5m



AP9870

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Product or component type	Power cord
Input Connection Type	IEC 60320 C14
Cable length	2.5 m
Number of cables	1

### Physical

Colour	Black
Height	3.8 cm
Width	7.6 cm
Depth	20.3 cm
Net weight	0.23 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

### Input

Network frequency	50/60 Hz
Permissible voltage	90...250 V
Max line current	10 A
Input current limits	10 A

### Output

Max current draw	10 A
Number of power socket outlets	1 IEC 60320 C13
Protection type	Without circuit breaker

### Conformance

Product certifications	CSA UL listed VDE
------------------------	-------------------------

### Environmental

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.100 cm
Package 1 Width	10.200 cm
Package 1 Length	20.300 cm
Package 1 Weight	295.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.370 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	38.960 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)


🌱 Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	73
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Use Better

♻️ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACH Regulation	<a href="#">REACH Declaration</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Halogen content performance	Product contains halogen above thresholds

💡 Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

🔄 Repack and remanufacture	
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Yes
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins