
Part Number : 733666330
Product Description : MCX Jack, Straight, Solder, RG-405 (.086" Semi-rigid), Brass Body, Gold (Au) Plated, One Piece Per Bag, 50 Ohms
Series Number : 73366
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

733666330_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-89675-183-001.pdf

PS-89675-365-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Straight, Solder, RG-405 (.086" Semi-rigid), Brass Body, Gold (Au) Plated, One Piece Per Bag, 50 Ohms
Application	RF
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	884982676831

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Jack
Keying to Mating Part	N/A

Downloaded from Arrow.com.

Net Weight	1.141/g
Orientation	Straight
Packaging Type	Individual Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-405, .086" Semi-Rigid Coaxial

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

Downloaded from Arrow.com.