

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	D70/22
Product ID:	1SNA400305R1000
EAN:	3472594003052
Catalog Description:	D70/22 Screw Clamp Terminal Blocks - Feed-through - Grey
Long Description:	- Closed terminal block: no end section needed, optimized rigidity.

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	22 mm
Product Net Height:	74 mm
Product Net Depth / Length:	75.4 mm
Product Net Weight:	158.1 g

Technical

Rated Cross-Section:	70 mm ²
Spacing:	22 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 16 ... 70 mm ² Screw Clamp / Flexible 2x 25 ... 35 mm ² Screw Clamp / Rigid 1x 16 ... 95 mm ² Screw Clamp / Rigid 2x 25 ... 35 mm ² Screw Clamp / With Insulated Ferrule 1x 50 mm ²
Gauge Type:	B11
Rated Current (I_n):	Main Circuit 192 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 8400 A

Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	6.1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	25.0 mm
Recommended Screw Driver:	6 mm
Tightening Torque:	acc. IEC 60947-1 6 N·m Manufacturer 7 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 4 ... 00 AWG Screw Clamp / Rigid 1x 4 ... 00 AWG
Connecting Capacity UL/CSA:	Stranded 0 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant

Certificates and Declarations (Document Number)

CB Certificate:	1SND161034A0202
CSA Certificate:	1SND161051A0202
cUL Certificate:	1SND161001A0209
Declaration of Conformity - CE:	1SND225014U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220001E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101

Classifications

Object Classification Code:	X
------------------------------------	---

ETIM 4: EC000897 - Feed-through terminal block

ETIM 5: EC000897 - Feed-through terminal block

ETIM 6: EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 10 piece

Package Level 1 Width: 138 mm

Package Level 1 Depth / Length: 151 mm

Package Level 1 Height: 78 mm

Package Level 1 Gross Weight: 1.581 kg

Package Level 1 EAN: 3472594003052

Package Level 2 Units: 30 piece

Package Level 2 Width: 200 mm

Package Level 2 Depth / Length: 300 mm

Package Level 2 Height: 200 mm

Package Level 3 Units: 3840 piece

Product Packing Type: Box

