





PRODUCT NUMBER	PITCH
VMxx55x000J0G	5.08 mm



Material:

- Item (a) Clamp: Steel zinc plated.
- Item (b) Terminal screw: Steel Zinc plating "-" slot type
- Item (c) Female contact: High conductivity copper, Tin plated
- Item (d) Terminal (top body): Thermoplastic (UL94V-0)
- Item (e) Terminal (bottom body): Thermoplastic (UL94V-0)
- Item (f) Clampage: Steel Zinc plated

Electrical cULus/TUV

- Voltage rating: 300VAC/300VAC
- Current rating: 20A/20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In / 0.4Nm
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval:  

N = Number of poles

Dim A=Nx5.08

Dim B=(N-1)x5.08

poles	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40

PART NO.: VM xx 55 x 0 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
0	2	Black (RAL9005)	
2	3	Red (RAL3001/D)	
3	4	Orange(RAL2011/P)	
4	5	Yellow(RAL1018/A)	
5	6	Green(RAL6018/T)	
6	8	Blue (RAL5015/A)	
8	9	Grey(RAL7035/D)	
9	9	White(RAL1102)	
C	24	Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family		
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
					angles	X.±0.5	TERMINAL BLOCK		
					flat	X.X±0.3	PLUGGABLE PLUG, WIHTOUT FLANGE		
					X*±1"	X.XX±0.1	scale		
					dr	EVIN ZHONG 042114	dwg no		
					enr	EVIN ZHONG 042114	sheet 1 of 1 size		
					chr	HANKE FENG 042114	VMxx55x000J0G		
					appd	SHI JUN 042114	type		
sheet index	revision	A					CUSTOMER Drawing		