

ZMV Series

Mini Size Snap-acting Switches



Agency Approvals

Agency	Agency File Number
US	E42363

Specifications

Contact Rating	3A 12VDC @ 100,000 cycles min. 3A 24VDC @ 50,000 cycles min. 3A 125/250VAC @ 10,000 cycles min. 0.01A 12/24VDC @ 1,000,000 cycles min. 0.01A 125/250VAC @ 1,000,000 cycles min.
Mechanical Life	1,000,000 cycles min.
Insulation Resistance	100 mΩ min.
Dielectric Strength	Min. 500VAC (50-60Hz)/minute between Live Parts
Operating Temperature	-40°C to 85°C
Operating Force	150 gf max.

Description

ZMV series mini snap-acting switches are often found used in automotive, medical, industrial and IoT devices. Featuring a unique pin plunger whereby actuation can be actuated from any angle.

Features & Benefits

- Compact size – ideal when space is limited
- High contact reliability to support from low range switching loads
- Adequate stroke setting for reliable & precision ON or OFF switching
- Pin plunger version can be actuated from an angle
- Internal spring design return – ensures the actuator is restored to the same position every time. These features yield consistent operation over the long life of these switches.
- IP67 for standalone switch except the metal terminal part; Full IP67 protection when potted with wire version
- RoHS compatible & compliant

Applications

- Automotive: door latch, seat position detection, EV charging
- Medical
- Industrial
- Home appliances
- IoT devices

Materials

Case	Nylon
Cover	
Actuator Button	PET+POM
Movable Contact	AG alloy (Gold plated if selected)
Stationary Contacts	
Terminals	Brass

Notes:

1. Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center. Sealing cap could possibly be damaged in case of contacts with oils or greases. Please try to avoid direct contact. If more support is needed, consult Customer Service Center.

ZMV Series

Mini Size Snap-acting Switches



Ordering Number



Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

ZMV - x - 150 - x - x - x - x - x

Series ZMV Electrical Rating 03A: 3A 125/250VAC (Contact silver plated) G03: 3A 125/250VAC (Contact gold plated) Operating Force 150: 150 grams Actuator Type P00: Pin plunger T13: Hinged lever with lever length 13 mm T20: Hinged lever with lever length 20 mm S03: Simulated hinged roller level length 15 mm L14: Leaf lever with lever length 14 mm L16: Simulated leaf roller lever length 16 mm L20: Leaf lever with lever length 20 mm	Wire Type for J, K, W Terminations NONE: AVSS 0.3 mm² (Default) 20: UL1007 20 AWG 22: UL1007 22 AWG 24: UL1007 24 AWG Pillar Type or Mounting Style A0: Standard (No support post) B5: Pillar type B 5 mm B2: Pillar type B 2 mm C5: Pillar type C 5 mm C2: Pillar type C 2 mm F0: Pillar type F 1.5 mm	Circuitry C: SPDT W: SPST N.C. Y: SPDT N.O. Terminations P: PC thru-hole S: Solder J: Wire leads out bottom K: Wire leads out right side W: Wire leads out left side
--	--	--

Series (mm)

ZMV Mini Size Snap-Acting Switches





ZMV Series

Mini Size Snap-acting Switches





Actuator Type (mm)

P00 Pin Plunger



T13 Hinged Lever with Lever Length 13 mm





ZMV Series



Mini Size Snap-acting Switches



T20 Hinged Lever with Lever Length 20 mm



S03 Simulated Hinged Roller Lever Length 15 mm




ZMV Series


Mini Size Snap-acting Switches



L14 Leaf Lever with Lever Length 14 mm



L16 Simulated Leaf Roller Lever Length 16 mm





ZMV Series

Mini Size Snap-acting Switches



L20 Leaf Lever with Length 20 mm




ZMV Series

Mini Size Snap-acting Switches




Terminations (mm)

P PC thru-hole



S Solder




ZMV Series

Mini Size Snap-acting Switches



J Wire Leads Out Bottom




Default wire:

COM: AVSS 0.3 mm² black or equivalent

NO: AVSS 0.3 mm² blue or equivalent

NC: AVSS 0.3 mm² gray or equivalent

K Wire Leads out Right Side



Default wire:

COM: AVSS 0.3 mm² black or equivalent

NO: AVSS 0.3 mm² blue or equivalent


NC: AVSS 0.3 mm² gray or equivalent

ZMV Series

Mini Size Snap-acting Switches



W Wire Leads Out Left Side



Default wire:


COM: AVSS 0.3 mm² black or equivalent

NO: AVSS 0.3 mm² blue or equivalent


NC: AVSS 0.3 mm² gray or equivalent

Pillar Type or Mounting Style

A0 Standard (No Support Post)



B5 Pillar Type B 5 mm




ZMV Series


Mini Size Snap-acting Switches



B2 Pillar Type B 2 mm



C5 Pillar Type C 5 mm





ZMV Series



Mini Size Snap-acting Switches



C2 Pillar Type C 2 mm



F0 Pillar Type F 1.5 mm









Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.

ZMV Series

Mini Size Snap-acting Switches



Switch Characteristics

Switch Type	Part Suffix	OF Max. (gf)	FP Max (mm)	OP (mm)	EP Min. (mm)	OT Min. (mm)	MD Max. (mm)	RF Min. (gf)
ZMVXXX150P00XXXX		150	11.2	10.4 ± 0.2	9.1	1.1	0.25	20
			7.2	6.4 ± 0.2	5.1			
ZMVXXX150T13XXXX			12.8	11.5 ± 0.5	10	1.0	0.5	13
			8.8	7.5 ± 0.5	6			
ZMVXXX150T20XXXX		95	15.5	13.3 ± 0.8	11	1.5	0.8	6
			11.5	9.3 ± 0.8	7			
ZMVXXX150S03XXXX		120	16.5	15.2 ± 0.5	13.5	1.2	0.5	10
			12.5	11.2 ± 0.5	9.5			
ZMVXXX150L14XXXX		220	13.3	11.4 ± 0.5	9.8	1.1		38
			9.3	7.4 ± 0.5	5.8			
ZMVXXX150L16XXXX		200	16.5	14.8 ± 0.5	12.9	1.4		
			12.5	10.8 ± 0.5	8.9			
ZMVXXX150L20XXXX		168	15.5	12.2 ± 0.8	9.9	1.5	0.8	30
			11.5	8.2 ± 0.8	5.9			

Note:

OF: Operating force, FP: Free position, OP: Operating position, EP: End position, OT: Overtravel, MD: Differential motion, RF: Release force