Outdoor 3G Radome Omni 2 dBi Antenna

Pulse Part Number RO8061/21702 Family



Pulse announces a new outdoor radome omni antenna for 3G operations. The frequency range covers 806-960 and 1710-2170 MHz with peak gain levels of 1.5 and 2.5 dBi delivered in the lower and higher frequency bands respectively. The white Pultruded Fiberglass radome is 216 mm (8.5 inches) in height, UV protected and IP-67 rated. It has been tested to wind loading of 150 mph. The antenna is designed for installation on a mast or external wall using the FB2BRACKET or FB3BRACKET.

Key applications are femto cells, 3G repeaters and small base stations. Given the frequency range covered by the RO8061/27102, this antenna is also suitable for other global cellular bands such as GPRS, EDGE, HSDPA, GSM, UMTS.

Features
- Frequency Range 806-960/1710-2170 MHz
- Omni Directional with 2 dBi Gain
- UV Protected and IP-67 Rated
- RoHS Compliant Product

Applications
- 3G Repeaters
- Femto Cell
- Small Base Station

PRELIMINARY

Part Number	Connector
RO8061/21702NM	N Male
RO8061/21702NF	N Female

Downloaded from Arrow.com.

Outdoor 3G Radome Omni 2 dBi Antenna

Pulse Part Number RO8061/21702 Family

Electrical Specifications

	Frequency 1 [MHz]	806-960
	Frequency 2 [MHz]	1710-2170
	Nominal Impedance [Ω]	50
VSWR	Freq 1	2.5:1
	Freq 2	2.5:1
Gain	Freq 1 [dBi avg]	1.5 Max
	Freq 2 [dBi avg]	2.5 Max
Polar-ization	Frequency 1	Horizontal Omni
	Frequency 2	Vertical - 60˚
	Power Rating [W]	20

Environmental Specifications

Operating Temperature [°C]	-40 to +85
Storage Temperature [°C]	-40 to +85
Relative Humidity [%]	100

Mechanical Specifications

Radome Material	Pultruded Fiberglass
Color	Off White
Ingress Protection	IP-67
Weight [oz/g]	5 / 156
Wind-loading [Mph]	150
Dimensions [Inches/Meters]	1 x 8.5 / 25.3 x 215.9
Flammability Rating	UL94 HB

PRELIMINARY


Downloaded from Arrow.com.

Outdoor 3G Radome Omni 2 dBi Antenna


Pulse Part Number RO8061/21702 Family

Radiation Patterns


Horizontal Plane - 806-960 MHz




Horizontal Plane - 1710-2170 MHz



Vertical Plane - 806-960 MHz



Vertical Plane - 1710-2170 MHz



PRELIMINARY

For More Information

Pulse Worldwide Headquarters
12220 World Trade Drive
San Diego, CA 92128
U.S.A.

Tel: 858 674 8100
Fax: 858 674 8262

Larsen Brand Antennas
3611 NE 112th Avenue
Vancouver, WA 98682
USA

Tel: 360 944 7551
Fax: 369 944 7556

Europe Headquarters
Pulse GmbH & Do, KG
Zeppelinstrasse 15
Herrenberg
Germany

Tel: 49 7032 7806 0
Fax: 49 7032 7806 135

Asia Headquarters
B402, Shenzhen Academy of
Aerospace Technology Bldg.
10th Kejinan Road, High-Tech Zone
Nanshan District, Shenzen, PR China 518057

Tel: 86 755 33966678
Fax: 86 755 33966700

Pulse North Asia
3F, No. 198, Zhongyuan Road
Zhongli City, Taoyuan County 320
Taiwan R. O. C.

Tel: 886 3 4356768
Fax: 886 3 4356823

Pulse (Suzhou) Wireless Products Co, Inc.
99 Huo Ju Road, (#29 Bldg, 4th Phase)
Suzhou New District
Science & Tech Industrial Park
Jiangsu Province, Suzhou 215009 PR China

Tel: 86 512 6807 9998
Fax: 86 512 6809 8023

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2010. Pulse Electronics, Inc. All rights reserved.

Downloaded from Arrow.com.