THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - ;- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED PER ECR-16-014661	26OCT2016	JH	TIM

1 SPECIFICATION: WIRE RANGE; #18–#34 AWG. 0.16–1.02 DIA [.006–.040] mm. COPPER MAGNET WIRE.


2 POCKET RECOMMENDATION: 1601424.


△3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114–13166. CONSULT PRODUCT ENGINEERING FOR PROPER INSERTION DEPTH.


△4 POST PLATED 2 – 3.8 MICRONS TIN OVER 2.5 MICRONS MIN COPPER.

△5 THIS LENGTH IS SELECTIVELY POST PLATED WITH 2–3.8 MICRONS SILVER OVER 1.25 MICRONS MIN NICKEL. SILVER MAY EXTEND ONTO CARRIER. BALANCE OF TERMINAL IS MICKEL PLATED ONLY.

△6 PRELIMINARY – NOT FOR PRODUCTION.







△5	2–1601203–3
△4	2–1601203–2
△4 △6	1601203–2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13[.005]
3 PLC ± –
4 PLC ± –
ANGLES ± 2°

MATERIAL: FULL HARD BRASS
FINISH: SEE TABLE

DWN M.S. FEHER 05OCT2004
CHK G. JACONO 05OCT2004
APVD G. JACONO 05OCT2004
PRODUCT SPEC 108–2085
APPLICATION SPEC △3 —
WEIGHT 0.000000

TE Connectivity

NAME: STANDARD RANGE WIRE TO .187 [4.75] X .020 [0.51], OFFSET TAB SIAMEZE TERMINAL

SIZE A1 | CAGE CODE 00779 | DRAWING NO Ⓒ-1601203 | RESTRICTED TO —

CUSTOMER DRAWING | SCALE 11:1 | SHEET 1 OF 1 | REV A3

Downloaded from Arrow.com.