

molex

Part Number : [1301530158](#)

Product Description : Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, Molded NEMA L6-20 Plug and Receptacle, 20A, 240V, 0.61m (2.0') Cord Length

Series Number : 130153

Status : Obsolete

Product Category : Power Distribution

Engineering Part Number : 24052-1MLDM



Documents and Resources

Drawings

[1301530158_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, Molded NEMA L6-20 Plug and Receptacle, 20A, 240V, 0.61m (2.0') Cord Length
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA L6-20
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678889734

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')

Cord Type	12/3 SJE00W
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Net Weight	0.836/kg
Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	GFCI Single

This document was generated on May 27, 2026

Obsolete