


SIZE
(A)

PART
No. WWR-1-E
DRWG

Note: This drawing is supplied for information only. Its content is the property of The Pyle-National Company. No rights of reproduction are implied. Prints in customers' files cannot be maintained to current issues.

REVISIONS				
LTR	ECO	DESCRIPTION	DATE	APPROVED
L	18884	NEW DWG: WAS DWG DATED 8/31/56	6/3/93	<i>WLT</i>



MATERIALS

CONTACT BODY - ANNEALED BRASS
CONTACT SHROUD - 1/4 HARD COPPER ALLOY
GROMMET - THERMOPLASTIC RUBBER

REQUIRED CRIMP TOOL

DANIELS MFR. CORP. CAT. NO. HX-23
PNEUMATIC CRIMP TOOL WITH Y543
CRIMP DIE

PERFORMANCE SPECIFICATION

1. WIRE RANGE - #14, #12, #10 AWG
2. CRIMP TENSILE STRENGTH WITH #14 AWG WIRE - 50 LBS. MINIMUM
3. CONTACT INSERTION/EXTRACT FORCE - 35 OZ. MAX. 8 OZ. MIN.

AMPHENOL SIDNEY INTEGRATION
FSCM NO. 49367
SPECIFICATION NO. 9-9380
DATE: 7-JULY-2001

		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON				DRAWN J.M.T.		P R		PYLE-NATIONAL COMPANY CHICAGO, ILLINOIS 60651			
		FRAC $\pm \frac{1}{64}$	DEC $\pm .005$	ANG $\pm 1^\circ$	FINISH $\checkmark$	DATE 6/3/93							
		MATERIAL SEE ABOVE				CHECKED		PRODUCT ENGINEER <i>WLT</i>		TITLE PIN CONTACT WITH GROMMET WWR SERIES RECEPTACLE			
								PRODUCTION ENGINEERING					
		FINISH CONTACT - SILVER PLATED, .000100 THICK				QUALITY CONTROL		SIZE A		CODE IDENT NO 49367		DRAWING NUMBER WWR-1-E	
NEXT ASSY		USED ON				ENGINEERING APPROVAL		SCALE				SHEET OF	
APPLICATION		SUPERSEDES SAME DATED 8/31/56				PART TYPE		S		C			