


MGPWT-00194-P	REV			
1879391-9	BA1			
Product Description	MGPWT-00194, XFMR T SMD SS Previously MGPWT-00194			
				
Primary Units are in inches millimetres in brackets				
Electrical Specifications at +20°C unless noted otherwise				
Test	Limits	Unit	Tol	Notes
Inductance	3.6	μH	±15%	1-4, 1.0MHz, 100mVAC, Ls.
Inductance	0.155	μH	±15%	2-5, 1.0MHz, 100mVAC, Ls.
Inductance	0.155	μH	±15%	3-6, 1.0MHz, 100mVAC, Ls.
DC Resistance	0.150	Ω	Max.	Pins 1 - 4
DC Resistance	0.035	Ω	Max.	Pins 2 - 5
DC Resistance	0.035	Ω	Max.	Pins 3 - 6
Turns Ratio	5.40 : 1	--	±4%	(1-4) : (2-5)
Turns Ratio	5.40 : 1	--	±4%	(1-4) : (3-6)
Dielectric	300	VDC	500μA	1-6 tie(2+3), 1 second test, 500μA maximum leakage current.
SRF	60.0	MHz	Min	Pins 1 - 4
Terminal plating is Hot Dipped SnAgCu				
Storage Temperature Range: -55°C to +155°C				
Shelf Life 12 Months from delivery date				
Operating Temperature Range: -40°C to +85°C				
260°C Maximum reflow temperature per J-STD-020B				
The information contained in this drawing is the sole property of Tyco Electronics. Any reproduction or use without the written permission of Tyco Electronics is prohibited.				
Specifications subject to change without notice. For latest revision visit http://www.tycoelectronics.com				
Page 1 of 1 Date 14.04.2016				