







PRODUCT NO
10046971-011LF

REV.	ECN	REV'D BY	DATE
A	DG06-0314	RYAN YUAN	08/03/06
B	DG06-0524	JULIA WANG	12/26/06



- NOTE:
- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA.(ONE SIDE)
MATTE PURE TIN 120u" OVER SOLDERING AREA.
 - PACKING SPEC. GS-14-937
 - PRODUCT SPEC. GS-12-338.
 - MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.

5. PART NUMBER 10046971-011LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.

CUSTOMER
COPY



DIMENSIONAL LIMITS APPLY AFTER
PLATING (IF SPECIFIED)

DO NOT SCALE DRAWING

GENERAL TOLERANCE

MILLIMETER INCH ANGLE

X.X ±0.8
X.XX ±0.25
X.XXX ±0.13
.XX ±0.03
.XXX ±0.010
.XXX ±0.005
±3°

DRAWN NAME DATE

CHECKED BEER FU 08/03/06

APPROVED JOSEPH HSIA 08/03/06



DESCRIPTION

POWER EDGE CONNECTOR
VERTICAL TYPE (31PX2)(4.00 TAIL)

SCALE SIZE DRAWING NO. REV SHEET

1:1 A4 10046971-011 B 1 OF 2



ALL RIGHT RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF F C I. COPYRIGHT F C I.

PDM: Rev:B

STATUS Released

Printed: Apr 09, 2010

2



DETAIL A
SCALE 5.000



DESCRIPTION

SCALE	SIZE	DRAWING NO.	REV	SHEET
1:1	A4	10046971-011	B	2 OF 2

MILLIMETER	INCH	ANGLE
X.X ±0.8	.XX ±0.03	±3°
X.XX ±0.25	.XXX ±0.010	
X.XXX±0.13	.XXXX±0.005	

	NAME	DATE
DRAWN	RYAN YUAN	08/03/06
CHECKED	BEER FU	08/03/06
APPROVED	JOSEPH HSIA	08/03/06

STATUS: **Released**

Printed: Apr 09, 2010