





PRODUCT NUMBER	PITCH
YK441xx0x0J0G	9.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



MATERIALS ELECTRICAL
 RATED VOLTAGE & CURRENT: cULus CQC 300 V, 30A / 300V 24A
 WITHSTAND VOLTAGE: AC2500V/min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 10.54 Lb-In. / 0.8Nm
 WIRE RANGE: 22 - 10 AWG / 22-14 AWG
 1) MOLDED PARTS: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3.5
 APPROVAL: cULus CQC

DIMENSION

Dim A	N×9.5±1.5
Dim B	(N-1)×9.5

N=Number of poles

Poles	Tolerance
2p-4p	±0.20
5p-8p	±0.25
9p-16p	±0.35
17p-23p	±0.40
24p-30p	±0.50

PART NO.: YK 441xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles

 30 30 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM	product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title TERMINAL BLOCK			
				angles	X.±0.5		BARRIER TYPE			
				linear	X.X±0.3		dwg no YK441xx0x0J0G			
				X*±1*	X.XX±0.1		sheet 1 of 1 size A4			
				dr	EVAN LU 061614		type CUSTOMER Drawing			
				enr	EVAN LU 061614					
				chr	HANKE FENG 061614					
				appd	SHI JUN 061614					
sheet index	revision sheet	A	1							