





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/10/05	
A		RELEASED	10/27/10	



RECOMMENDED PCB LAYOUT



SPECIFICATION:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator Color: Black

Metal Latch: Zinc Alloy, Nickel plated.

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Operating Voltage: 350V AC max.

Current rating: 3 Amps max.

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 1000 VAC / minute

Temperature Rating:

Operating temperature: -40°C TO +105°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.

Positions: 06, 08, 10, 14, 16, 20, 26, 30, 34, 40, 50, 60, 64
A = .100 [2.54] X No. of Positions / 2 + .300 [7.62]
B = .100 [2.54] X No. of Positions / 2 + .088 [2.24]
C = .100 [2.54] X No. of Positions / 2 - .100 [2.54]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BOX HEADER, HORIZONTAL PCB MOUNT,
2 ROW .100 PITCH, GOLD PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES			
X	± .10	Ø X	± .10
.XX	± .020	Ø XX	± .015
.XXX	± .015	Ø XXX	± .010
APPROVALS		DATE	
DRAWN	SS	5/10/05	
CHECKED			
APPROVED			
TITLE		REV.	
SIZE		PART NO.	
X		BHR-XX-HUA-ML	
REF:		SCALE: NTS	
S00019C		SHEET 1 OF 1	