
**Part Number :** 391002508
**Product Description :** 15.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 8 Circuits
**Series Number :** 39100
**Status :** Active
**Product Category :** Terminal Blocks and Barrier Strip
**Engineering Part Number :** M800-04-08-5-M1



## Documents and Resources

### Drawings

391002508_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Terminal Blocks and Barrier Strip |
| Series | 39100 |
| Description | 15.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 8 Circuits |
| Application | Wire-to-Wire |
| Component Type | One Piece |
| Keyword | Terminal Strip |
| Product Name | Eurostyle Two Screw |
| Type | Terminal Strips |
| UPC | 78172545264 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 63.0A |
| Voltage - Maximum | 600V |

### Physical

| | |
|---|---|
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | White |
| Entry Angle | Horizontal |
| Lock to Mating Part | No |
| Material - Metal | Stainless Steel, Steel |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Resin | Nylon |
| Net Weight | 62.670/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| Panel Mount | Mounting Holes Between Circuit |
| Pitch - Mating Interface | 15.00mm |
| Pitch - Termination Interface | 15.00mm |
| Polarized to Mating Part | N/A |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Screw |
| Wire Size (AWG) | 6, 8, 10, 12, 14 |
| Wire Size $mm^2$ | 2.00-13.50 |



Downloaded from Arrow.com.