



Dry-Shrink™ HSTT12-48-Q45 Heat Shrink

HSTT12-48-Q45

The HSTT12-48-Q45 Thin Wall Heat Shrink Tubing shrinks around wires, connectors, joints, and terminals when heated to protect against abrasion. Applications include insulating and protecting wires/cables in indoor, dry locations. Shrink ratio: 3:1. Temperature range: -67°F to 275°F (-55°C to 135°C). Flame retardant, cross-linked polyolefin. .12" (3.2mm) Diameter, Color: Yellow/Green, 25 pc. per pkg.

Specifications

Product Type	Heat Shrink Tubing
Adhesive Lined	No
Color	Yellow/Green
Material	Cross-Linked Polyolefin
Maximum Operating Temperature (°C)	135
Maximum Operating Temperature (°F)	275
Minimum Operating Temperature (°C)	-55
Minimum Operating Temperature (°F)	-67
Nominal Diameter (In.)	0.125
Nominal Diameter (mm)	3.2
Nominal Recovered Wall Thickness (In.)	0.02
Nominal Recovered Wall Thickness (mm)	0.5
Sub Brand	Dry-Shrink™
Overall Length (In.)	48
Overall Length (ft.)	4
Overall Length (m)	1.22
Overall Length (mm)	1219
Resistance Properties	Flame-Retardant
Standards Met	UL Recognized, CSA Approved, MIL SPEC
Shrink Ratio	3:1
Shrink Temperature (°C)	90
Shrink Temperature (°F)	194
Maximum Recovered Inside Diameter (In.)	0.062
Maximum Recovered Inside Diameter (mm)	1.6
Minimum Expanded Inside Diameter (In.)	0.12
Minimum Expanded Inside Diameter (mm)	3.2
Application	For Dry Locations

Packaging Detail

UPC	07498352059
Std. Pkg. Qty.	25
Std. Pkg. Volume (cf)	0.1950
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000