



**NO O-RING
REQUIRED!**

Heyco® -Tite Liquid Tight Cordgrips

Multi-Hole with Integral Sealing Ring

Sequenced by Conductor Size

The Ultimate in Liquid Tight Strain Relief Protection

- Heyco® **Multi-hole glands** provide the widest range of conductor through-hole size and number configurations, many of which are agency approved. See the tabular charts for specific approvals for specific parts. These approvals are not "global" or implied approvals; they are both real and part specific.
- Integral Sealing Ring ensures a superior seal at the clearance or threaded mounting hole location, every time.
- IP 68 rated.
- Cordgrips are made of nylon construction with TPE sealing glands that resist salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents.
- For body part dimensions see page 3-1, 3-3, and 3-4.
- Multi-hole glands are only to be used with Heyco Liquid Tight Cordgrips and are not sold separately.
- Consult Heyco for Cordgrips molded in other colors.


CONDUCTORS		 or 	NPT HUB*		PG HUB**		METRIC HUB**	
Hole Size mm.	No.		specifications on page 3-1		specifications on page 3-3		specifications on page 3-4	
			Black Part No.	Desc.	Black Part No.	Desc.	Black Part No.	Desc.
Round, Open Holes – consult Heyco for Snap-in-2 Hub versions								
1,4	4		M3228GAP	LTCG 3/8	M3210GAP	LTCG 9	M4336GAP	LTCG M16
	6		M3228GAZ	LTCG 3/8	M3210GAZ	LTCG 9	M4336GAZ	LTCG M16
	10		M3228GE	LTCG 3/8	M3210GE	LTCG 9	M4336GE	LTCG M16
1,5	2		M4516GBA	LTCG 1/4	M3207GBA	LTCG 7	M4332GBA	LTCG M12
	3		—	—	M3213GF	LTCG 11	—	—
1,6	5		M3228GG	LTCG 3/8	M3210GG	LTCG 9	M4336GG	LTCG M16
1,7	2		M3228GH	LTCG 3/8	M3210GH	LTCG 9	M4336GH	LTCG M16
	3		M3228GJ	LTCG 3/8	M3210GJ	LTCG 9	M4336GJ	LTCG M16
	4		M3228GK	LTCG 3/8	M3210GK	LTCG 9	M4336GK	LTCG M16
2,0	3		M3231GL	LTCG 1/2	M3216GL	LTCG 13	M4340GL	LTCG M20
2,3	4		M3228GM	LTCG 3/8	M3210GM	LTCG 9	M4336GM	LTCG M16
2,5	2		M3231GN	LTCG 1/2	M3216GN	LTCG 13	M4340GN	LTCG M20
2,8	4		—	—	M3213GAY	LTCG 11	—	—
3,0	2		M3228GP	LTCG 3/8	M3210GP	LTCG 9	M4336GP	LTCG M16
			—	—	M3213GB	LTCG 11***	—	—
			—	—	M3213GP	LTCG 11	—	—
	3		—	—	M3213GQ	LTCG 11	—	—
			M3231GQ	LTCG 1/2	M3216GQ	LTCG 13	M4340GQ	LTCG M20
			M3200GQ	LTCG LL 1/2	M3219GQ	LTCG 16	—	—
		4	M3200GR	LTCG LL 1/2	M3219GR	LTCG 16	—	—
	6		M3231GS	LTCG 1/2	M3216GS	LTCG 13	M4340GS	LTCG M20
			M3200GS	LTCG LL 1/2	M3219GS	LTCG 16	—	—
	3,8	2		M3231GT	LTCG 1/2	M3216GT	LTCG 13	M4340GT
6			M3200GW	LTCG LL 1/2	M3219GW	LTCG 16	—	—
4,0	2		—	—	M3213GAK	LTCG 11	—	—
	3		M3231GX	LTCG 1/2	M3216GX	LTCG 13	M4340GX	LTCG M20
			M3200GX	LTCG LL 1/2	M3219GX	LTCG 16	—	—
	4		M3200GY	LTCG LL 1/2	M3219GY	LTCG 16	—	—
	5		M3200GZ	LTCG LL 1/2	M3219GZ	LTCG 16	—	—
6		M3200GBB	LTCG LL 1/2	M3219GBB	LTCG 16	—	—	

Standard color black.

***Locknuts not included.** For Locknut specifications or to order Locknuts separately, see pages 3-47 & 3-48.

****Unassembled Nylon Locknuts INCLUDED.**

*****Short Thread**



Multi-hole Gland (typical)

*Quick
Specs*

Material	Nylon 6/6 with TPE Sealing Gland
Flammability Rating	94V-2 Standard
Temperature Range	Static -40°F (-40°C) to 239°F (115°C) Dynamic -4°F (-20°C) to 212°F (100°C)
IP Rating	IP 68