

CA-06P1N12T008S - Cable connector



1619371

<https://www.phoenixcontact.com/us/products/1619371>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, series: CA, angled, shielded: yes, SPEEDCON, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 10 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1243489



Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1619371 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB31 |
| Product key | ABRAED |
| Catalog page | Page 90 (C-2-2019) |
| GTIN | 4046356824767 |
| Weight per piece (including packing) | 192.8 g |
| Weight per piece (excluding packing) | 192 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-06P1N12T008S - Cable connector



1619371

<https://www.phoenixcontact.com/us/products/1619371>

Technical data

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Insulating body

| | |
|---|---------------------|
| Coding | N |
| Insulation body material | PBT |
| Contact material | CuZn |
| Contact surface material | Ni/Au |
| Insertion/withdrawal cycles | 100 |
| Connection method | Solder connection |
| Contact switching type | Pin |
| Application | Signal |
| Number of positions | 6 |
| Direction of rotation | Standard |
| Connection profile | 6 |
| Rated voltage | 48 V AC |
| | 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Contact diameter Signal contacts | 2 mm |
| Litz wire cross-section Signal contacts max. | 2.5 mm ² |
| Nominal current per signal contact | 20 A |

Housing

| | |
|-----------------------------------|----------|
| Housing material | Metal |
| Type of locking | SPEEDCON |
| Pg screw connection | none |
| Degree of protection (plugged in) | IP67 |
| Thread type | M23 |

Seal

| | |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
| Seal material | NBR |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

CA-06P1N12T008S - Cable connector


1619371

<https://www.phoenixcontact.com/us/products/1619371>



Drawings

Dimensional drawing



Dimensional drawing


CA-06P1N12T008S - Cable connector

1619371

<https://www.phoenixcontact.com/us/products/1619371>



Schematic diagram



CA-06P1N12T008S - Cable connector



1619371

<https://www.phoenixcontact.com/us/products/1619371>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619371>

| cUL Recognized Approval ID: E335019-20141210 | | | | |
|---|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 48 V | 10 A | - 14 | - |

| UL Recognized Approval ID: E335019-20141210 | | | | |
|--|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 48 V | 20 A | - 14 | - |

| cULus Recognized | | | | |
|------------------|--|--|--|--|
|------------------|--|--|--|--|

CA-06P1N12T008S - Cable connector



1619371

<https://www.phoenixcontact.com/us/products/1619371>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-06P1N12T008S - Cable connector



1619371

<https://www.phoenixcontact.com/us/products/1619371>

Environmental product compliance

| | |
|------------|--|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 years |
| | For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads" |

CA-06P1N12T008S - Cable connector

1619371

<https://www.phoenixcontact.com/us/products/1619371>



Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/us/products/1607456>

Torque screwdriver, series: RC



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/us/products/1607455>

Hook wrench, series: RC



CA-06P1N12T008S - Cable connector

1619371

<https://www.phoenixcontact.com/us/products/1619371>



RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/us/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/us/products/1620592>

Color coding, color: orange



CA-06P1N12T008S - Cable connector

1619371

<https://www.phoenixcontact.com/us/products/1619371>



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/us/products/1620593>

Color coding, color: black



PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/us/products/1577206>

Plastic protective cap, M23, degree of protection: IP20, series: CA



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com