

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.





The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU for RoHS compliant.



ORIGINAL



REVISIONS			
SYM	ECN No.	DESCRIPTION	DATE
A	NE-20033	APPROVED REVISION	03/12/2020
			APPROVED
			Roger Tsai



RECOMMENDED P.C.B LAYOUT
TOLERANCE: ±0.05

TOLERANCE		APPROVALS		DATE	TITLE		UNIT		SIZE	PART No.	
X.		DRAWN	Debby Hung	03/12/2020	GSB3 SERIES, USB 3.0 A TYPE, RECEPTACLE, SINGLE PORT, R/A, SINK, DIP TYPE		mm		A3	GSB311RXXXC1HR	
X.X	±0.30	CHECKED	Sandy Wu	03/12/2020			SCALE		1 OF 2		
X.XX	±0.20	APPROVED	Roger Tsai	03/12/2020			NA				
X.XXX	±0.10	DWG TYPE	CUST DWG	PROJECT CODE			OTHER				
ANGULAR	±1°										
UNLESS OTHERWISE SPECIFIED											

NOTES:

- MATERIAL:
HOUSING: PA4T HF, UL94V-0, COLOR: OPTION.
TERMINAL(5P): COPPER ALLOY.
TERMINAL(4P): COPPER ALLOY.
SHELL: SUS201.
- FINISH:
TERMINAL:
CONTACT AREA: SELECTED GOLD PLATING THICKNESS MIN.;
SOLDERING AREA: MATTE TIN PLATING 100 μ" THICKNESS MIN.;
UNDER PLATING: NICKEL PLATING 50μ" THICKNESS MIN. OVERALL.
SHELL:
NICKEL PLATING 50 μ" THICKNESS MIN.OVERALL.
- PRODUCT SPECIFICATION REFER TO : PS-7425.
- THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS PER DIRECTIVE 2011/65/EU FOR RoHS COMPLIANT.
OR PER IEC 61249-2-21 FOR HALOGEN-FREE COMPLIANT.




This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.
The marking on this product doesn't contain environmental hazardous materials per directive 2011/65/EU for RoHS compliant.



ORIGINAL





REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A	NE-20033	APPROVED REVISION	03/12/2020	Roger Tsai



NOTES:

1. MATERIAL:
CARRIER TAPE: PS.
COVER TAPE: PET.
REEL: PS.
SHIPPING BOX: CORRUGATED FIBERBOARD.
2. DIMENSION:
REEL: $\phi = 330$.
SHIPPING BOX: L=350, W=350, H=240.
3. PEELING STRENGTH: 0.1~1.3N(10~130 GRAMS)
4. PEELING SPEED: 300mm/min.

PACKAGING BY T&R	6.3	4.8	400	6	2400	GSB311RXXXC1HR
	G/W KG	N/W KG	PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	PART NUMBER

TOLERANCE		APPROVALS		DATE		TITLE		Amphenol®			
X. X.X ±0.30 X.XX ±0.20 X.XXX ±0.10		DRAWN Debby Hung		03/12/2020		GSB3 SERIES, USB 3.0 A TYPE, RECEPTACLE, SINGLE PORT, R/A, SINK, DIP TYPE		Amphenol Corporation			
		CHECKED Sandy Wu		03/12/2020				Amphenol Taiwan Corporation			
		APPROVED Roger Tsai		03/12/2020							
ANGULAR ±1°								UNIT mm	SIZE A3	PART No. GSB311RXXXC1HR	
UNLESS OTHERWISE SPECIFIED		DWG TYPE CUST DWG		PROJECT CODE OTHER				SCALE NA	SHEET 2 OF 2	DWG No. GSB311RXXXC1HR	REV. A