



Pushing Performance  
Since 1945

# M12-L fem. 5p A-cod. with conduit M17x1



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 21 03 812 2511  |
| Specification      | M12-L fem. 5p A-cod. with conduit M17x1                                       |
| HARTING eCatalogue | <a href="https://harting.com/21038122511">https://harting.com/21038122511</a> |

## Identification

|               |                          |
|---------------|--------------------------|
| Category      | Connectors               |
| Series        | Circular connectors M12  |
| Element       | Cable connector          |
| Specification | with conduit<br>Straight |

## Version

|                    |   |
|--------------------|---|
| Termination method | Crimp termination                       |
| Gender             | Female                                  |
| Shielding          | Shielded                                |
| Number of contacts | 4<br>5                                  |
| Coding             | A-coding                                |
| Locking type       | Screw locking                           |
| Details            | Please order crimp contacts separately. |

## Technical characteristics

|                               |                               |
|-------------------------------|-------------------------------|
| Conductor cross-section       | 0.14 ... 0.75 mm <sup>2</sup> |
| Conductor cross-section [AWG] | AWG 26 ... AWG 18             |
| Wire outer diameter           | ≤2.3 mm                       |
| Rated current                 | 4 A                           |
| Rated voltage                 | 48 V AC<br>60 V DC            |
| Rated impulse voltage         | 1.5 kV                        |



**Pushing Performance**  
Since 1945

## Technical characteristics

|   |                             |
|---|-----------------------------|
| Pollution degree                          | 3                           |
| Overvoltage category                      | III                         |
| Insulation resistance                     | $>10^8 \Omega$              |
| Contact resistance                        | $\leq 10 \text{ m}\Omega$   |
| Tightening torque                         | 0.6 Nm                      |
| Wrench size (knurled screw / knurled nut) | 17                          |
| Limiting temperature                      | -40 ... +85 °C              |
| Mating cycles                             | $\geq 500$                  |
| Degree of protection acc. to IEC 60529    | IP65 / IP67 mated condition |
| Cable diameter                            | 4.5 ... 8.8 mm              |
| Isolation group                           | I ( $600 \leq \text{CTI}$ ) |

## Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| Material (insert)                    | Polyamide (PA)       |
| Material (hood/housing)              | Zinc die-cast        |
| RoHS                                 | compliant            |
| ELV status                           | compliant            |
| China RoHS                           | e                    |
| REACH Annex XVII substances          | Not contained        |
| REACH ANNEX XIV substances           | Not contained        |
| REACH SVHC substances                | Not contained        |
| California Proposition 65 substances | Yes                  |
| California Proposition 65 substances | Lead                 |
|                                      | Nickel               |
|                                      | Naphthalene          |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels   | R26                  |

## Specifications and approvals

|                |                                   |
|----------------|-----------------------------------|
| Specifications | IEC 61076-2-101                   |
| UL / CSA       | UL 1977 ECBT2.E102079             |
|                | CSA-C22.2 No. 182.3 ECBT8.E102079 |

## Commercial data

|                |   |
|----------------|---|
| Packaging size | 1 |
|----------------|---|



**Pushing Performance**  
Since 1945

Commercial data

|                                |  |
|--------------------------------|--|
| Net weight                     | 45 g   |
| Country of origin              | Romania  |
| European customs tariff number | 85366990   |
| GTIN                           | 5713140139565                                    |
| ETIM                           | EC002635   |
| eCl@ss                         | 27440116 Circular connector (for field assembly) |