

COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle cable plug (male)
16_SMA-50-2-20/199_N

Properties

- Suitable for use with Eacon_2C cable
- Applicable in frequencies up to 6 GHz
- Compliant with MIL-STD-348A/310 interface standard



Product configuration		
Interface type	Gender	Standard
SMA	plug	HUBER+SUHNER-SMA-26.5GHz

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless Steel	
Body	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 6 GHz	24.9 dB	1.12
6.01 GHz ... 11 GHz	16.5 dB	1.35

Mechanical data	
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle cable plug (male)
16_SMA-50-2-20/199_N

Environmental data		
Operation temperature	-40 °C ... 150 °C	
Ingress protection (IP Rating)	Mated / IP67	
Ordering Information Table		
Item number	Item description	Packaging type
85074235	16_SMA-50-2-20/199_NE	Single
Suitable cables		
Cable group	U92 - EACON_2C	
Suitable cables	EACON_2C	
Additional Information		
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3032 / Date of publication: 17.07.2024 / uncontrolled copy