

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image





In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

General ordering data

Version	Z-series, Fuse terminal, Rated cross-section: 6 mm², Tension-clamp connection, black, Direct mounting
Order No.	<u>1814690000</u>
Туре	ZSI 6-2/FC
GTIN (EAN)	4032248358489
Qty.	25 pc(s).

Technical data



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Depth	50 mm	Depth (inches)	1.969 inch
Depth including DIN rail	51 mm	Height	70 mm
Height (inches)	2.756 inch	Width	8.1 mm
Width (inches)	0.319 inch	Net weight	20.6 g
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
Material data			
Material	Wemid	Colour	black
UL 94 flammability rating	V-0		black
System specifications			
	- · · · ·		
Version	Tension-clamp connection, Fuse cartridge, Without LED, for plug-in cross-con- nector, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No
Additional technical data			
Explosion-tested version	No	Installation advice	Direct mounting
Open sides	right	Type of mounting	Snap-on
CSA rating data			
Certificate No. (CSA)	200039-1152892	Current size C (CSA)	25 A
Voltage size C (CSA)	300 V	Wire cross section max. (CSA)	10 AWG
Wire cross section min. (CSA)	22 AWG		
Conductors for clamping (add	litional connection)		
Conductor cross-section, flexible plus		Connection direction	
plastic collar DIN 46228/1, further con	1-		
nection, max.	6 mm ²		Inclined / angled



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

4.0 x 0.8 mm	Clamping range, max.	10 mm²
	Connection cross-section, stranded,	<u> </u>
		6 mm ²
		top
	·	2
10 mm		Tension-clamp connection
Tension-clamp connection	max.	AWG 8
AWG 26	stranded, max.	10 mm ²
0.5 mm²	ly stranded with wire-end ferrules DIN	6 mm²
0.5 mm²	Wire connection cross-section, fine- ly stranded with wire-end ferrules DIN 46228/4, max.	6 mm²
0.5 mm²	Wire connection cross-section, solid core, max.	10 mm²
0.5 mm²		
AC/DC		
Blade fuse type ATO/stan- dard	Display	Without LED
pluggable	Operating voltage, max.	250 V
1.9 W at 24.0 A @ 28°C	Power loss for short-circuit protection only for an individual arrangement	3.0 W at 30.0 A @ 24°C
AC/DC		
AC/DC		
	Bail	TS 35
Direct mounting DIN 72581-3, IEC	Rail Wire connection cross section AWG, max	TS 35
Direct mounting		TS 35 AWG 8
Direct mounting DIN 72581-3, IEC 60947-7-3	Wire connection cross section AWG,	-
Direct mounting DIN 72581-3, IEC 60947-7-3 AWG 26	Wire connection cross section AWG, max.	AWG 8
Direct mounting DIN 72581-3, IEC 60947-7-3 AWG 26 6 mm ²	Wire connection cross section AWG, max. Rated voltage	AWG 8 250 V
Direct mounting DIN 72581-3, IEC 60947-7-3 AWG 26 6 mm ² 250 V	Wire connection cross section AWG, max. Rated voltage Rated DC voltage	AWG 8 250 V 250 V
Direct mounting DIN 72581-3, IEC 60947-7-3 AWG 26 6 mm ² 250 V 30 A DIN 72581-3, IEC	Wire connection cross section AWG, max. Rated voltage Rated DC voltage Current at maximum wires Volume resistance according to IEC	AWG 8 250 V 250 V 30 A
Direct mounting DIN 72581-3, IEC 60947-7-3 AWG 26 6 mm ² 250 V 30 A	Wire connection cross section AWG, max. Rated voltage Rated DC voltage Current at maximum wires	AWG 8 250 V 250 V
	0.33 mm ² h. 0.5 mm ² A5 10 mm Tension-clamp connection AWG 26 0.5 mm ² 0.5 mm ² 0.5 mm ² 0.5 mm ² AC/DC Blade fuse type ATO/stan- dard pluggable 1.9 W at 24.0 A @ 28°C	0.33 mm² Connection cross-section, stranded, max. n. 0.5 mm² Connection direction A5 Number of connections 10 mm Type of connection cross section AWG, max. AWG 26 Wire connection cross section, finely stranded, max. 0.5 mm² Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. 0.5 mm² Vire connection cross-section, solid core, max. 0.5 mm² Vire connection cross-section, solid core, max. 0.5 mm² Display AC/DC Display Blade fuse type ATO/standard Display 1.9 W at 24.0 A @ 28°C Over loss for short-circuit protection only for an individual arrangement

Technical data



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

UL rating data				
Certificate No. (cURus)		Conductor size Factory wiring r	nav (cl.l.	
Certificate No. (Contas)	E60693	Rus)	10 AWG	
Conductor size Factory wiring r		Conductor size Field wiring ma		
Rus)	22 AWG		10 AWG	
Conductor size Field wiring mir	ւ (cURus) 22 AWG	Voltage size C (cURus)	300 V	
Classifications				
ETIM 6.0	EC000899	ETIM 7.0	EC000899	
ETIM 8.0	EC000899	ETIM 9.0	EC000899	
ETIM 10.0	EC000899	ECLASS 9.0	27-14-11-16	
ECLASS 9.1	27-14-11-16	ECLASS 3.0	27-14-11-16	
ECLASS 11.0	27-14-11-16	ECLASS 10.0	27-14-11-16	
ECLASS 13.0	27-25-01-13	ECLASS 12.0		
ECLASS 15.0 ECLASS 15.0	27-25-01-13	ECLASS 14.0	27-25-01-13	
LCLA33 13.0	27-23-01-13			
Environmental Product Co	mpliance			
RoHS Compliance Status	Compliant without exem	notion		
REACH SVHC	No SVHC above 0.1 wt%	•		
Important note				
Product information	The voltage depends on	the selected fuse element or the selected indi	icator light	
Approvals				
Approvals	(€ @	c 🔁 us 🗔) UK	
Approvals MAMID	mdcop.weidmueller.com mdcop.weidmueller.com mdcop.weidmueller.com	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https:// mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/ https:// mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/ https:// mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/ https:// mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/		
ROHS	Conform	., siddenter, , renamen, 000_010200/-11		
UL File Number Search	UL Website			
Certificate No. (cURus)	E60693			
Downloads				
Approval/Certificate/Documen				
formity	<u>CB Certificate</u>			
	<u>CB Certificate</u>			
	CB Certificate DNV Certificate			
	Div Certificate Declaration of Confor	mity		
	UKCA declaration of c			
		dards EN 45545-2_2020-10		
Engineering Data	CAD data – STEP			
User Documentation	StorageConditionsTer	rminalBlocks		
Catalogues	Catalogues in PDF-for			
<u>~</u>				

Creation date May 23, 2025 10:14:23 AM CEST

Brochures



Weidmüller Interface GmbH & Co. KG Klingenbergstraße 26

D-32758 Detmold Germany

www.weidmueller.com

Drawings









Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Z-Series



that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

Weidmüller's range of products includes end brackets

General	ordering data	
Туре	ZEW 35/2	Version
Order No.	<u>8630740000</u>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 8 mm, 100 °C
GTIN (EAN)	4032248348916	
Qty.	20 pc(s).	
Туре	ZEW 35	Version
Order No.	<u>954000000</u>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 6 mm, 100 °C
GTIN (EAN)	4008190956264	
Qty.	20 pc(s).	
Туре	ZST 1	Version
Order No.	<u>1269070000</u>	Accessories, Accessories holder
GTIN (EAN)	4050118094091	
Qty.	25 pc(s).	

Blank



ZS markers - in proven MultiCard-format - have been developed specifically for the Z-series. They have a large printing area. The hinged mechanism even allows access to cross-connectors without dismantling. Quick installation is guaranteed by the fact that the single tags are clipped on in strips. The single tags are easy to separate.

- Hinged marker area
- · Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	ZS 12/6 MC NE WS	Version
Order No.	<u>1610020000</u>	ZS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller,
GTIN (EAN)	4008190444600	Allen-Bradley, white
Qty.	400 pc(s).	

Accessories

WS 12/6





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wearresistant labelling. A print resolution of 300 dpi also produces a very legible script. **Your benefits with MultiMark**

• Firm hold and durable printing

- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

	· · · · · · · · · · · · · · · · · · ·	
Туре	WS 12/6 MM WS	Version
Order No.	<u>2007200000</u>	WS, Terminal marker, 12 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118391886	
Qty.	600 pc(s).	

Accessories

WS 12/6.5





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wearresistant labelling. A print resolution of 300 dpi also produces a very legible script. **Your benefits with MultiMark**

_.

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

Туре	WS 12/6.5 MM WS	Version
Order No.	<u>2619930000</u>	WS, Terminal marker, 12 x 6.5 mm, Weidmueller, white
GTIN (EAN)	4050118626155	
Qty.	600 pc(s).	

Test plugs



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Туре	PS 2.3 RT	Version
Order No.	0180400000	Test adapter (terminal), 230 V, 20 mA
GTIN (EAN)	4008190060121	
Qty.	20 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank

-		-	-	-	-	÷
						I
						l
						1
			-			÷
						ł
						1
						ċ
			-		-	÷
						1
						1
						ī,
1						ì
1						1
			I			
			I			
			T			

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Zseries. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

· Can be fitted in strips or individually

• Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 12/6 MC NE WS	Version
Order No.	<u>1609900000</u>	WS, Terminal marker, 12 x 6 mm, Pitch in mm (P): 6.00 Weidmueller,
GTIN (EAN)	4008190203467	Allen-Bradley, white
Qty.	600 pc(s).	

Z-Series



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Туре	ZTA 7/ZA	Version
Order No.	<u>1780670000</u>	Accessories, Test adapter, 9 A
GTIN (EAN)	4032248180202	
Qty.	25 pc(s).	

Accessories



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include

marking options, also for group markers, and also a test

W-Series

W Series

General ordering data

Туре	WEW 35/1	Version
Order No.	<u>1059000000</u>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 12 mm, 100 °C
GTIN (EAN)	4008190172282	
Qty.	50 pc(s).	
Туре	WEW 35/2	Version
Order No.	<u>1061200000</u>	End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C
Order No. GTIN (EAN)	<u>1061200000</u> 4008190030230	End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C

plug holder.

Custom printing

F	
h	000000
h	10000000
F	
F	000000338
ŀ	00000008
h	10000000
h	
ŀ	

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data Type DEK 5/6 MC SDR Version Order No. 1609830000 Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00 GTIN (EAN) 4008190456603 Weidmueller, To customer specification Oty. 200 pc(s). 200 pc(s).



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank

Π	11		Π	1
	11		T	
-	11		T	1
i	П		Г	i
i			T	1
	11		T	1

WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Zseries. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

· Can be fitted in strips or individually

• Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	WS 12/6.5 MC NE WS	Version
Order No.	<u>1609920000</u>	WS, Terminal marker, 12 x 6.5 mm, Pitch in mm (P): 6.50
GTIN (EAN)	4008190203511	Weidmueller, Allen-Bradley, white
Qty.	540 pc(s).	

Z-Series



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

General ordering data

	0	
Туре	ZAD 2/4	Version
Order No.	<u>1609080000</u>	Z-series, Cover
GTIN (EAN)	4008190263317	
Qty.	20 pc(s).	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

6 mm² The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

mm²

	J	
Туре	ZQV 6/3 GE	Version
Order No.	<u>1627860000</u>	Accessories, Cross-connector, 41 A
GTIN (EAN)	4008190200435	
Qty.	60 pc(s).	
Туре	ZQV 6/32 GE	Version
Order No.	<u>1733640000</u>	Accessories, Cross-connector, 41 A
GTIN (EAN)	4008190994334	
Qty.	10 pc(s).	
Туре	ZQV 6/2 GE	Version
Order No.	<u>1627850000</u>	Accessories, Cross-connector, 41 A
GTIN (EAN)	4008190200428	
Qty.	60 pc(s).	
Туре	ZQV 6/4 GE	Version
Order No.	<u>1627870000</u>	Accessories, Cross-connector, 41 A
GTIN (EAN)	4008190200442	
Qty.	60 pc(s).	
Туре	ZQV 6/24 GE	Version
Order No.	<u>1908990000</u>	Accessories, Cross-connector, 41 A
GTIN (EAN)	4032248535309	
Qty.	10 pc(s).	

Slotted screwdriver



Accessories

ZSI 6-2/FC



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

6 mm² End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof. mm^2 **General ordering data**

Туре	ZAP ZDU6-2 SW	Version
Order No.	<u>1814710000</u>	Z-series, End plate
GTIN (EAN)	4032248359417	
Qty.	50 pc(s).	

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon[®] Connect modular terminal blocks. Fitting marker types could be found under the

respective accessories of the designation marking holder.

General ordering data		
Туре	BZT 1 WS 10/5	Version
Order No.	<u>1805490000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	
czty.	100 pc(3).	
сту. Туре	BZT 1 ZA WS 10/5	Version
		Version Accessories, Marker holder
Туре	BZT 1 ZA WS 10/5	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

Circuit breakers



Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

Туре ETA 1180 01 7A Version Order No. 1279050000 Miniature fuse, 7 A GTIN (EAN) 4050118091434 Qty. 5 pc(s). ETA 1180 01 3.5A Туре Version Order No. 1279010000 Miniature fuse, 3.5 A 4050118091397 GTIN (EAN) Qty. 5 pc(s). Туре ETA 1180 01 0.3A Version 1278870000 Order No. Miniature fuse, 0.3 A 4050118091472 GTIN (EAN) Qty. 5 pc(s). ETA 1180 01 2A Туре Version Order No. 1278970000 Miniature fuse, 2 A 4050118091489 GTIN (EAN) Qty. 5 pc(s). Туре ETA 1180 01 5A Version Order No. 1279030000 Miniature fuse, 5 A GTIN (EAN) 4050118091465 Qty. 5 pc(s). ETA 1180 01 0.4A Туре Version 1278880000 Order No. Miniature fuse, 0.4 A GTIN (EAN) 4050118091380 Qty. 5 pc(s). Туре ETA 1180 01 2.5A Version Order No. 1278980000 Miniature fuse, 2.5 A GTIN (EAN) 4050118091403 Qty. 5 pc(s). Туре ETA 1180 01 0.7A Version Order No. 1278930000 Miniature fuse, 0.7 A GTIN (EAN) 4050118091519 Qty. 5 pc(s). ETA 1180 01 1A Туре Version 1278950000 Order No. Miniature fuse, 1 A GTIN (EAN) 4050118091366 5 pc(s). Qty. Туре ETA 1180 01 8A Version

 Order No.
 1279060000
 Miniature fuse, 8 A

 GTIN (EAN)
 4050118091410

Creation date May 23, 2025 10:14:23 AM CEST

Qty.

5 pc(s).

Accessories

ZSI 6-2/FC



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Туре	ETA 1180 01 0.5A	Version
Order No.	1278910000	Miniature fuse, 0.5 A
GTIN (EAN)	4050118091359	
Qty.	5 pc(s).	
Туре	ETA 1180 01 0.8A	Version
Order No.	1278940000	Miniature fuse, 0.8 A
GTIN (EAN)	4050118091526	
Qty.	5 pc(s).	
Туре	ETA 1180 01 10A	Version
Order No.	1279070000	Miniature fuse, 10 A
GTIN (EAN)	4050118091427	
Qty.	5 pc(s).	
Туре	ETA 1180-01-1.5A	Version
Order No.	1278960000	Miniature fuse, 1.5 A
GTIN (EAN)	4050118091540	
Qty.	5 pc(s).	
Туре	ETA 1180 01 3A	Version
Order No.	1278990000	Miniature fuse, 3 A
GTIN (EAN)	4050118091298	
Qty.	5 pc(s).	
Туре	ETA 1180 01 0.1A	Version
Order No.	1278840000	Miniature fuse, 0.1 A
GTIN (EAN)	4050118091373	
Qty.	5 pc(s).	
Туре	ETA 1180 01 4A	Version
Order No.	1279020000	Miniature fuse, 4 A
GTIN (EAN)	4050118091496	
Qty.	5 pc(s).	
Туре	ETA 1180 01 0.25A	Version
Order No.	1278860000	Miniature fuse, 0.25 A
GTIN (EAN)	4050118091441	
Qty.	5 pc(s).	
Туре	ETA 1180 01 6A	Version
Order No.	1279040000	Miniature fuse, 6 A
GTIN (EAN)	4050118091502	
Qty.	5 pc(s).	
Туре	ETA 1180 01 0.6A	Version
Order No.	<u>1278920000</u>	Miniature fuse, 0.6 A
GTIN (EAN)	4050118091533	
Qty.	5 pc(s).	
Туре	ETA 1180 01 0.2A	Version
Order No.	1278850000	Miniature fuse, 0.2 A
GTIN (EAN)	4050118091458	
Qty.	5 pc(s).	

Accessories

SAK-Series

SAK Series

General ordering data



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General	General ordering data			
Туре	EW 35 GR 7032	Version		
Order No.	0383530000	End bracket, grey, TS 35, V-0, Wemid, Width: 9 mm, 120 °C		
GTIN (EAN)	4008190027322			
Qty.	50 pc(s).			
Туре	EW 35/SCHA/M3	Version		
Order No.	0258660000	End bracket, beige, TS 35, V-2, Wemid, Width: 16.5 mm, 100 °C		
GTIN (EAN)	4008190033477			
Qty.	20 pc(s).			
Туре	EW 35	Version		
Order No.	0383560000	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C		
GTIN (EAN)	4008190181314			
Qty.	50 pc(s).			