



Part Number : [2250540871](#)

Product Description : 1.50mm Pitch, Micro-Lock Plus PCB Header, Single Row, Right Angle, Surface Mount, Tin-Bismuth Plating, Positive Lock, 8 Circuits, Black

Series Number : 225054

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2250540871 sd.pdf](#)

[2250549200-SPK-200.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2250520000-PS-000.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|----------------|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 225054 |
| Description | 1.50mm Pitch, Micro-Lock Plus PCB Header, Single Row, Right Angle, Surface Mount, Tin-Bismuth Plating, Positive Lock, 8 Circuits, Black |
| Application | Signal, Wire-to-Board |
| Component Type | PCB Header |
| Keyword | Micro-Lock Plus 1.5 |
| Product Name | Micro-Lock Plus |
| UPC | 198930045557 |

Agency

| | |
|----|--------|
| UL | E29179 |
|----|--------|

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 3.8A |
| Voltage - Maximum | 125V AC (RMS)/DC |

Physical

| | |
|--------------------------------|-----------------------|
| Breakaway | No |
| Circuits (Loaded) | 8 |
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin-Bismuth |
| Material - Plating Termination | Tin-Bismuth |
| Material - Resin | Polyamide (PA) |
| Net Weight | 393.300/mg |
| Number of Rows | 1 |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Retention | No |
| Pitch - Mating Interface | 1.50mm |
| Pitch - Termination Interface | 1.50mm |
| Plating min - Mating | 1.000µm |
| Plating min - Termination | 1.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Robotic Placement | Vacuum Pick-Up Area |
| Shrouded | Shrouded |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Surface Mount |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|--|---------------|
| 1.50mm Pitch, Micro-Lock Plus Single Row Receptacle Housings | <u>225052</u> |

This document was generated on May 13, 2026