



Part Number : [346916082](#)

Product Description : Stac64 Right-Angle Header Assembly, Plastic Pin-Alignment-Plate, 8 Circuits, Polarization C, Brown, Tray

Series Number : 34691

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[346916082_sd.pdf](#)

[PK-31300-892-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[347290200-AS-CH-000.pdf](#)

[PS-34729-020-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Boric acid per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	34691
Description	Stac64 Right-Angle Header Assembly, Plastic Pin-Alignment-Plate, 8 Circuits, Polarization C, Brown, Tray
Application	Automotive, Power, Wire-to-Board
Comments	Polarization C
Component Type	PCB Header
Product Name	Stac64
UPC	887191003603

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	8

Circuits (maximum)	8
Color - Resin	Brown
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.157/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Stac64 Receptacle Housings	<u>34729</u>

This document was generated on Apr 30, 2026