

**Part Number :** [1715769238](#)

**Product Description :** Impact 100 Ohm 6-Pair Right-Angle Orthogonal Direct Header, Bottom Guided, with Outtrigger, 12 Column, 72 Differential Pair, 270° Mate Position, Pin Length 5.50mm, Plated Through-Hole Dimension 0.39mm, Lead Free

**Series Number :** 171576

**Status :** Active

**Product Category :** Backplane Connectors



---

## Documents and Resources

### Drawings

[1715769238 sd.pdf](#)

[PK-70873-8024-001.pdf](#)

[PK-70873-8025-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-76060-9999-001.pdf](#)

[AS-76850-990-001.pdf](#)


[PS-45499-002-001.pdf](#)

[PS-76060-999-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

	61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Backplane Connectors
Series	171576
Description	Impact 100 Ohm 6-Pair Right-Angle Orthogonal Direct Header, Bottom Guided, with Outrigger, 12 Column, 72 Differential Pair, 270° Mate Position, Pin Length 5.50mm, Plated Through-Hole Dimension 0.39mm, Lead Free
Application	Orthogonal Direct
Component Type	PCB Header
Product Name	Impact
UPC	887191724812

### Agency

UL	E29179
----	--------

## Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

## Physical

Circuits (Loaded)	216
Circuits (maximum)	216
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	46.905/g
Number of Columns	12
Number of Pairs	6
Number of Rows	18
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.40mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm

Plating min - Mating	0.762µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
Impact 100 Ohm 6 Pair Right-Angle Orthogonal Daughtercards	<u>76290</u>

---

This document was generated on Apr 14, 2026