8830 A

AC axial panel compact fan



ebm-papst St. Georgen GmbH & Co. KG
Hermann-Papst-Str. 1
D-78112 St. Georgen
Phone +49 (0) 7724 81-0
info2@de.ebmpapst.com
www.ebmpapst.com

Nominal data

Item	**8830 A**
Motor	**-0**

Phase		1~
Nominal voltage	VAC	115
Frequency	Hz	60
Speed (rpm)	min^{-1}	1950
Power consumption	W	8.0
Min. ambient temperature	°C	-10
Max. ambient temperature	°C	80
Air flow	m^3/h	34
Sound power level	B	4.3
Sound pressure level	dB(A)	29

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment
Subject to change

Downloaded from Arrow.com.

AC axial panel compact fan

Technical description


Weight	0.490 kg
Dimensions	80 x 80 x 38 mm
Impeller material	Metal
Housing material	Metal
Airflow direction	Intake over struts
Service life L10 at 40 °C	62500 h
Service life L10 at maximum temperature	25000 h
Option	Optionally available with electrical hookup to leads. Optionally available with exhaust over struts and clockwise rotation.

ebm-papst St. Georgen GmbH & Co. KG · Hermann-Papst-Str. 1 · D-78112 St. Georgen · Phone +49 (0) 7724 81-0 · info2@de.ebmpapst.com · www.ebmpapst.com

Downloaded from Arrow.com.

AC axial panel compact fan

Product drawing




ebm-papst St. Georgen GmbH & Co. KG · Hermann-Papst-Str. 1 · D-78112 St. Georgen · Phone +49 (0) 7724 81-0 · info2@de.ebmpapst.com · www.ebmpapst.com

Downloaded from Arrow.com.

AC axial panel compact fan

Curves: Air performance



ebm-papst St. Georgen GmbH & Co. KG · Hermann-Papst-Str. 1 · D-78112 St. Georgen · Phone +49 (0) 7724 81-0 · info2@de.ebmpapst.com · www.ebmpapst.com

Downloaded from Arrow.com.