molex



Part Number : 936014181
Product Description : Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 2 Levers, Top Entry, Size 32A «66x40», M32 Thread, High Construction, Grey
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7832.4657.5

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 2 Levers, Top Entry, Size 32A «66x40», M32 Thread, High Construction, Grey
Component Type	Double Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191885995

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V

Physical

Component Size	32A «66x40»
Entry Location	Top
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Hood	Die-cast Aluminum
Material - Lever	Stainless Steel
Net Weight	313.000/g
Number of Levers	2
Packaging Type	Bag
Thread Size	M32
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 32A «66x40» S-A and S-D Inserts

Downloaded from Arrow.com.