

MICRO SWITCH

a Honeywell Division

FED. MFG. CODE 91929

Ø.250 -

.829±.010 ¬

1.222±.030

1.000 MAX

Ø .688±.030-

FREE POSITION

M 4602EN222-R

DR AW I NG NUMBER

വ

A 204384

— . 392

.050

LOGIC LEVEL CIRCUIT

ANSI YI4.5M-1982 APPLIES

SWITCH - ENCLOSED **ASSEMBLY** 

4602EN222-R

DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ± .030 TWO PLACES (.00) ±.015 THREE PLACES (.000)  $\pm .005$ ANGLES

WEIGHT

THIRD ANGLE PROJECTION

⊕ -=--

4602EN222-R

INSULATION RESISTANCE

 $(500 \text{ VDC } \pm 10\%)$ 

1000 Megohm MIN

1000 Megohm MIN

1000 Megohm MIN