







THIS DRAWING IS UNPUBLISHED.
 RELEASED FOR PUBLICATION
 ALL RIGHTS RESERVED.

LOC		DISP		REVISIONS			
P	LTR	DESCRIPTION	DATE	OWN	APVD		
ES	00						
A		INITIAL RELEASE	14AUG2012	SY	AC		



NOTES:

- ⚠ MATERIAL CONTACT; PHOSPHORBRONZE
MATERIAL HOUSING;
GLASSFILLED POLYESTER UL-RATING 94VO (GRAY)
- ⚠ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27μm NICKEL MIN.
AND ACTION PIN: 0,5μm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
- ⚠ CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR ON THE BACK SIDE.
- ⚠ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID. 95 HOLES
FITS WITH INTEGRATED GROUND RETURN UPSHIELD,
BASIC P.N. 352028
AND INTEGRATED GROUND RETURN LOWERSHIELD,
BASIC P.N. 352029
- ⚠ CONNECTOR ASSEMBLED WITH ALTERNATE FEMALE CONTACTS.
- ⚠ 1,27μm MIN GOLD PLATING AT MATING SURFACES, NO LUBRICANT.



THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0-PLC	±0,2
1-PLC	
2-PLC	
3-PLC	
4-PLC	
ANGLES	
FINISH	
MATERIAL	

FINISH		MATERIAL		2170349-5	
OW	SANDERS YAN	OW			
APVD	ALEX CAI	APVD			
PRODUCT SPEC		PRODUCT SPEC			
108-19082		108-19082			
APPLICATION SPEC		APPLICATION SPEC			
114-19029		114-19029			
WEIGHT		WEIGHT			
CUSTOMER DRAWING		CUSTOMER DRAWING			