

5

4

3

2

1


NOTES:

1. MATERIALS AND FINISHES:
BNC STR PLUG - BRASS, NICKLE PLATING
CABLE - RG 58


2. ELECTRICAL:
A. IMPEDANCE: 50 OHM

3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-850-292-XXX AND DATE CODE".

SCALE 0.400



LENGTH 'L' (SEE TABLE)



ADHESIVE LINED
HEAT SHRINK TUBE
TYP(2)

25.40 REF
[1.000]
TYP(2)

INTERFACE PER
MIL-STD-348
SERIES: BNC PLUG
TYP(2)

LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-850-292-006	-	6.00 [0.152]
-	95-850-292M025	9.84 [0.250]
95-850-292-012	-	12.00 [0.305]
95-850-292-018	-	18.00 [0.457]
-	95-850-292M050	19.69 [0.500]
95-850-292-024	-	24.00 [0.610]
-	95-850-292M075	29.53 [0.750]
95-850-292-036	-	36.00 [0.914]
-	95-850-292M100	39.37 [1.000]
95-850-292-048	-	48.00 [1.219]
-	95-850-292M150	59.06 [1.500]
95-850-292-060	-	60.00 [1.524]
95-850-292-072	-	72.00 [1.829]
-	95-850-292M200	78.74 [2.000]
-	95-850-292M300	118.11 [3.000]
95-850-292-120	-	120.00 [3.048]
95-850-292-144	-	144.00 [3.658]
95-850-292-180	-	180.00 [4.572]
-	95-850-292M500	196.85 [5.000]
95-850-292-300	-	300.00 [7.620]
-	95-850-292M10L	393.70 [10.000]
95-850-292-600	-	600.00 [15.240]
-	95-850-292M20L	787.40 [20.000]
95-850-292-900	-	900.00 [22.860]
-	95-850-292M30L	1181.10 [30.000]
95-850-292L100	-	1200.00 [30.480]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

☒ FREQUENCY: DC - 6 GHz

☒ CONTINUITY

☐ VSWR: ____ 1 MAX.

☒ HI-POT: 750 VRMS

☐ INS. LOSS: ____ dB MAX.

☐ OTHER

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

THIRD ANGLE PROJ.

REFERENCE

EAR#
11142

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE:
<0.5mm = ±0.05mm [≤0.020 = ±0.002]
0.5 - 6mm = ±0.1mm [≥0.020 - 0.236 = ±0.004]
>6.00 - 30mm = ±0.2mm [≥0.236 - 1.181 = ±0.008]
>30.00 - 120mm = ±0.3mm [≥1.181 - 4.725 = ±0.012]

ANGLES = ±1°

MATERIAL

SEE NOTES

ENGR.1
D INESH A

ENGR.2

DATE
25-JAN-22

TITLE
BNC STR PLUG IP 67 TO
BNC STR PLUG IP 67 USING
RG 58 CABLE VARIOUS LENGTH

SHEET NO. 2 OF 2

SCALE: 1.8:1.0

Amphenol RF

SIZE
B

DRAWING NO. 95-850-292-XXX

ITEM NO. 95-850-292-XXX

PART NO. 95-850-292-XXX

REV
A

5

4

3

2

1

Downloaded from Arrow.com

5

4

3

2

1