


# LR44R

Alkaline manganese batteries are suitable for various applications such as toys, medical devices and health appliances. All models are 100% made in Japan, and environmentally friendly (0% mercury).

In Production

REACH

## Appearance & Shape



### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# LR44R



## Specifications

Battery type	Alkaline Manganese Batteries
Nominal Voltage	1.5V
Nominal Capacity	150mAh
Operating Temperature Range	-10°C to 60°C
Diameter (inch)	0.457inch
Diameter (mm)	11.6mm
Height (inch)	0.213inch
Height (mm)	5.4mm
IEC (JIS)	LR44
Mass (oz)	0.0705oz
Mass (g)	2g

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.