



## NOTES:

1. END 'A' MATE WITH 6.00±0.20mm THICKNESS SILVER PLATING BUSBAR
2. ALL CABLE ASSEMBLIES SHALL 100% OPEN/SHORT TEST
3. SILVER PLATING CONTACT MAY DISCOLOR IN AIR, BUT NO PERFORMANCE ISSUE
4. AS LONG AS WIRE PIN ASSIGNMENT IS CORRECT, THE DIFFERENT COLOR CABLE LINE ON TOP OR BOTTOM CAN BE ACCEPTED. CROSS POINT POSITION IS ALSO NOT LIMITED.
5. MOUNTING HARDWARE:  
2xM3 SCREWS  
2x20mm dia. WASHERS  
TORQUE SPEC: 0.4~0.6 N.M



## BK150 CONNECTOR



## 3D VIEW

spec ref	dr	Andy Zhuang	2/11'23	<b>Amphenol Power Solutions</b> A Division of Amphenol Corporation amphenol-icc.com	MM	scale	NA	size	A3
tolerance std	eng	Andy Zhuang	2/11'23		ecr no				
TOLERANCES UNLESS OTHERWISE SPECIFIED	rvwr	Siny Hu	2/11'23		rel level				
	appr	Siny Hu	2/11'23						
surface	linear	0.X	±0.3	projection	title		10162876-1SP120LF		rev
	linear	0.XX	±0.25						
	linear	0.XXX	±		product family		Product - Customer Drw		A
	angular	0°	±°						
					BK150		sheet 1 of 2		

Crosstec/KPM/PAZ/REV A/2020-07-13

