


NOTES:

1. MATERIALS AND FINISHES:

HD-BNC STR CRIMP PLUG - 34-1025
1.0/2.3 PUSH-PULL CRIMP PLUG - 282135-75
CABLE - BELDEN 1505A

2. ELECTRICAL:

A. IMPEDANCE: 75 OHM



HD-BNC STR
CRIMP PLUG

LENGTH "L" (SEE TABLE)

BELDEN 1505A CABLE

1.0/2.3 PUSH-PULL
CRIMP PLUG

LENGTH TABLE

PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH "L" IN INCHES [METERS]
95-850-156-006	-	6.00 [0.152]
	95-850-156M025	9.84 [0.250]
95-850-156-012	-	12.00 [0.305]
95-850-156-018	-	18.00 [0.457]
-	95-850-156M050	19.69 [0.500]
95-850-156-024	-	24.00 [0.610]
-	95-850-156M075	29.53 [0.750]
95-850-156-036	-	36.00 [0.914]
-	95-850-156M100	39.37 [1.000]
95-850-156-048	-	48.00 [1.219]
-	95-850-156M125	49.21 [1.250]
-	95-850-156M150	59.06 [1.500]
95-850-156-060	-	60.00 [1.524]
95-850-156-072	-	72.00 [1.829]
-	95-850-156M200	78.74 [2.000]
-	95-850-156M300	118.11 [3.000]
95-850-156-120	-	120.00 [3.048]
95-850-156-180	-	180.00 [4.572]
	95-850-156M500	196.85 [5.000]
95-850-156-300	-	300.00 [7.620]
-	95-850-156M10L	393.70 [10.000]
95-850-156L050	-	600.00 [15.240]
-	95-850-156M20L	787.40 [20.000]
95-850-156L075	-	900.00 [22.860]
-	95-850-156M30L	1181.10 [30.000]
95-850-156L100	-	1200.00 [30.480]

DESIGN REQUIREMENTS:

FREQUENCY: DC TO 4 GHz

CONTINUITY

VSWR ---- MAX

HI-POT : 500 VRMS

INS. LOSS ---- dB MAX

OTHER


UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES
±.015 (0.381 mm) ±.005 (0.127 mm) ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permit such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

THIRD ANGLE PROJ.

REVISONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG	5/15/15	50350	NR/BCG
B	HST REMOVED	6/30/15	50581	NR/BCG



SCALE 0.750

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

Amphenol RF

www.amphenolrf.com

DRAWING NO. 95-850-156-XXX

ITEM NO. 95-850-156-XXX

PART NO. 95-850-156XXXX

MATERIAL SEE NOTES	DRAWN CLEMENT	DATE 09-Dec-14
	ENGINEER CLEMENT	DATE 09-Dec-14
REFERENCE EAR # 6515	APPROVED K. CAPOZZI	DATE 6/30/15
	CONFIGURATION LEVEL: In Work	CAD FILE
FINISH	DWG SIZE B	REV B

TITLE
HD-BNC STR CRIMP PLUG TO
1.0/2.3 PUSH-PULL CRIMP PLUG,
USING BELDEN 1505A CABLE,
VARIOUS LENGTH

SCALE: 3.0:1.0 SHEET 2 OF 2

DWG SIZE
BREV
B