


CATALOG LISTING
PAGE 1 OF 1
ISSUE **M**
3
RELEASE NO. PR-22883
CHECK
REVISIONS
A CO-92539 CSL 4 MAY 98
B 205419 JLH 22 APR 02
CHECK
14 AUG 97
JAF
CHECK
14 AUG 97
TSM
DRAWN
RASTER




NOTES

- 1 - UNIT INCLUDES CATALOG LISTING 2X 1SM1 BASIC SWITCH
- 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3 - TERMINALS ARE PLATED FOR SOLDERING
- (4) HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805
- 5 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA312-AT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE - - - - 2.25 LBS MAX	CONTACT ARRANGEMENT 2X S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
	250 VAC - - - - - 5 AMP	ONE PLACE	(.0)	±.030
	30 VOLTS DC RATING	TWO PLACE	(.00)	±.015
	INDUCTIVE - - - - SEA LEVEL - - - - 3 AMP	THREE PLACE	(.000)	±.005
	RESISTIVE - - - - SEA LEVEL - - - - 5 AMP	ANGLES		±
	50,000 - - - - - 5 AMP			
	MAXIMUM INRUSH - - - - - 24 AMP			
		WEIGHT	.06 LB	